

# Dry Type Transformers General Purpose Encapsulated Single-Phase NEMA 3R

## Section 10

### .050 - 3 kVA Indoor/Outdoor Type QB UL Listed C-UL Listed

Input Voltage	Output Voltage	kVA	Frequency (Hz)	Taps	Wiring Diagram No. <sup>1</sup>	Weight (Lbs)	Frame Size	Product Number
120 x 240 Volts	120/240 Volts	0.05	60 Hz	No Taps	1	6	6100	9T51B0022
120 x 240 Volts	120/240 Volts	0.1	60 Hz	No Taps	1	6	6200	9T51B0024
120 x 240 Volts	120/240 Volts	0.15	60 Hz	No Taps	1	10	8175	9T51B0025
120 x 240 Volts	120/240 Volts	0.25	60 Hz	No Taps	1	10	8175	9T51B0027
120 x 240 Volts	120/240 Volts	0.5	60 Hz	No Taps	1	16	10200	9T51B0028
120 x 240 Volts	120/240 Volts	0.75	60 Hz	No Taps	1	25	12200	9T51B0029
120 x 240 Volts	120/240 Volts	1	60 Hz	No Taps	1	25	12225	9T51B0030
120 x 240 Volts	120/240 Volts	1.5	60 Hz	No Taps	1	40	14200	9T51B0031
120 x 240 Volts	120/240 Volts	2	60 Hz	No Taps	1	45	14250	9T51B0032
120 x 240 Volts	120/240 Volts	3	60 Hz	No Taps	1	60	14400	9T51B0033
208 Volts	120/240 Volts	0.5	60 Hz	No Taps	4	16	10200	9T51B0158
208 Volts	120/240 Volts	0.75	60 Hz	No Taps	4	25	12200	9T51B0159
208 Volts	120/240 Volts	1	60 Hz	No Taps	4	25	12225	9T51B0160
208 Volts	120/240 Volts	2	60 Hz	No Taps	4	45	14250	9T51B0156
208 Volts	120/240 Volts	3	60 Hz	No Taps	4	55	14350	9T51B0157

### .050 - 3 kVA Indoor/Outdoor Type QB UL Listed C-UL Listed

Input Voltage	Output Voltage	kVA	Frequency (Hz)	Taps	Wiring Diagram No. <sup>1</sup>	Weight (Lbs)	Frame Size	Product Number
277 Volts	120/240 Volts	0.25	60 Hz	(-2 5.1%)	2	10	8175	9T51B0187
277 Volts	120/240 Volts	0.5	60 Hz	(-2 5.1%)	2	16	10200	9T51B0188
277 Volts	120/240 Volts	0.75	60 Hz	(-2 5.1%)	2	25	12200	9T51B0189
277 Volts	120/240 Volts	1	60 Hz	(-2 5.1%)	2	30	12275	9T51B0190
277 Volts	120/240 Volts	1.5	60 Hz	(-2 5.1%)	2	40	14200	9T51B0191
277 Volts	120/240 Volts	2	60 Hz	(-2 5.1%)	2	45	14250	9T51B0192
277 Volts	120/240 Volts	3	60 Hz	(-2 5.1%)	2	55	14350	9T51B0193
380/400/416 Volts	120/240 Volts	0.05	50 Hz	No Taps	2	6	6150	9T51B0162
380/400/416 Volts	120/240 Volts	0.15	50 Hz	No Taps	2	10	8175	9T51B0165
380/400/416 Volts	120/240 Volts	0.25	50 Hz	No Taps	2	10	8200	9T51B0167
380/400/416 Volts	120/240 Volts	0.5	50 Hz	No Taps	2	20	10225	9T51B0168
380/400/416 Volts	120/240 Volts	0.75	50 Hz	No Taps	2	25	12200	9T51B0169
380/400/416 Volts	120/240 Volts	1	50 Hz	No Taps	2	30	12275	9T51B0170
380/400/416 Volts	120/240 Volts	1.5	50 Hz	No Taps	2	40	14225	9T51B0171
380/400/416 Volts	120/240 Volts	2	50 Hz	No Taps	2	50	14300	9T51B0172
380/400/416 Volts	120/240 Volts	3	50 Hz	No Taps	2	60	14400	9T51B0173

<sup>1</sup>See page 10-45 for wiring diagrams.

