

Modular Metering Meter Mod III

Meter Stack Modules
Three-Phase
Plus Accessories

Section 2



TMPR312140RB

Product Features

- Three-Phase/Four-Wire, 240-120 Vac; Three-Phase/Four-Wire, 208Y/120 Vac
- UL listed
- 1200 amp, 4-wire cross bus (aluminum)
- Front Accessible Field Phase Balancing by Meter Socket
- (1) 14-2 Equipment Ground per Socket, Factory Installed
- Swingaway Mounting Feet Factory Installed
- Only 225A and 400A sockets, Ringless Type, contain lever bypass. 125A + 200A meter sockets do not contain lever bypass.

Ringless Type Socket w/Lever Bypass

Socket Amps	No. of Sockets	Product Number
225A	1	TMPR312122R
225A	2	TMPR312222R
225A	3	TMPR312322R
225A	4	TMPR312422R
400A	1	TMPR312140TR ¹
400A	1	TMPR312140RB ²
400A	2	TMPR312240RB ³
400A	1	TMPK312140RB
400A	1	TMPK312140RBA

Ring Type Socket

Socket Amps	No. of Sockets	Product Number
200A	1	TMP38120RT ⁴
200 A	2	TMP312220RT ⁴
200A	3	TMP312320RT ⁴

Tenant Main Circuit Breakers 10,000 AIC

Socket Amps	Ampere Rating	Product Number
225/400/200	15	TEB132015 ⁵
225/400/200	20	TEB132020 ⁵
225/400/200	25	TEB132025 ⁵
225/400/200	39	TEB132030 ⁵
225/400/200	35	TEB132035 ⁵
225/400/200	40	TEB132040 ⁵
225/400/200	45	TEB132045 ⁵
225/400/200	50	TEB132050 ⁵
225/400/200	60	TEB132060 ⁵
225/400/200	70	TEB132070 ⁵
225/400/200	80	TEB132080 ⁵
225/400/200	90	TEB132090 ⁵
225/400/200	100	TEB132100 ⁵
225/400/200	125	TQD32125
225/400/200	150	TQD32150
225/400/200	175	TQD32175
225/400/200	200	TQD32200
225/400/200	225	Use TMQD

Tenant Main Circuit Breakers 22,000 AIC

Socket Amps	Ampere Rating	Product Number
225/400/200	100	THQD32100
225/400/200	125	THQD32125
225/400/200	150	THQD32150
225/400/200	175	THQD32175
225/400/200	200	THQD32200
225/400/200	225	Use TMQD

Tenant Main Circuit Breakers 100,000 AIC

Socket Amps	Ampere Rating	Product Number
225/400/200	60	TMQD32060
225/400/200	70	TMQD32070
225/400/200	80	TMQD32080
225/400/200	90	TMQD32090
225/400/200	100	TMQD32100
225/400/200	125	TMQD32125
225/400/200	150	TMQD32150
225/400/200	175	TMQD32175
225/400/200	200	TMQD32200
225/400/200	225	TMQD32225

Accessories – Field Installed

Type	Description	Product Number
TEB Breaker		TMTEB
Mounting Kit		
Barrel Lock Bracket and Guard Kit		TMBL ⁶
Bypass Kit	Totalizing Jumper Type	TMBPT320 ^{6,7}
Replacement Phase Balancing Jumper Kit		TMPJ31 ⁶
Blank Meter Socket Cover	Fits all positions	TMCB322A
Individual Meter Socket Barrier Kit (Includes 6)		TMBR3
Insulator for Lever		TMHN
By-pass Handle		
Mounting Z Rail	4-foot	TMZR
Spacer	4 inch, 4 cross bus rated, 1200A	TMPS12
Elbow	16 inch x 16 inch, 4 cross bus rated 1200A	TMPE12 ⁸
Elbow	12 inch x 12 inch, 4 cross bus rated 1200A	TMPE12A ⁸

¹Requires two tenant main breakers, 400 amp maximum sum of branch ratings.

Cannot be used to serve a single 400A load.

²400 Amp tenant breaker included, 65 kAIC.

³Two 400 Amp tenant breakers included.

⁴Meets EUSERC requirements. "T" suffix indicates EUSERC test bypass kit included.

⁵Requires one TMTEB per breaker.

⁶Not UL listed.

⁷180 amps continuous.

⁸Indoor, Type 1, for inside corners only.

