

# Molded Case Circuit Breakers Industrial Circuit Breaker Accessories

## Rating Plugs

### 60-600A Circuit Breakers, Electronic Trip, Spectra® RMS , with MicroVersaTrip® PM Trip Unit<sup>1</sup>

#### MicroVersaTrip® Plus and PM Rating Plug Selection –

All Plugs List Price \$106.00, GO-135S

Circuit Breaker Frame	Sensor Rating	Rating Plug Rating (Amperes)	Rating Plug Product No.
SGHB, SGHH, SGLB, SGLL, SGPB, SGPP	150	60	SRPG150B60
		80	SRPG150B80
		100	SRPG150B100
		125	SRPG150B125
		150	SRPG150B150
		400	SRPG400B150
	400	200	SRPG400B200
		225	SRPG400B225
		250	SRPG400B250
		300	SRPG400B300
		350	SRPG400B350
		400	SRPG400B400
		600	SRPG600B300
		400	SRPG600B400
	600	450	SRPG600B450
		500	SRPG600B500
		600	SRPG600B600

<sup>1</sup>MicroVersaTrip® PM Trip Units require 24 Vdc control power and voltage sensing signals. Refer to pages 1-12 to 1-14.

Note: All Spectra® breakers UL listed as HACR type.

All Spectra® breakers marked CE.

### 300-1200A Circuit Breakers, Electronic Trip, Spectra® RMS, SK1200 with MicroVersaTrip® Plus and PM<sup>1</sup>

#### MicroVersaTrip® Plus and PM Rating Plug Selection –

All Plugs List Price \$106.00, GO-135S

Circuit Breaker Frame	Sensor Rating	Rating Plug Rating (Amperes)	Rating Plug Product No.
SKHB, SKHH, SKLB, SKLL, SKPB, SKPP	800	300	SRPK800B300
		400	SRPK800B400
		500	SRPK800B500
		600	SRPK800B600
		700	SRPK800B700
		800	SRPK800B800
		600	SRPK1200B600
		700	SRPK1200B700
	1200	800	SRPK1200B800
		1000	SRPK1200B1000
		1200	SRPK1200B1200 <sup>2</sup>

<sup>1</sup>MicroVersaTrip® PM Trip Units require 24 Vdc control power and voltage sensing signals. Refer to pages 1-12 to 1-14.

<sup>2</sup>Not suitable for use with 100% rated, 1000A breaker frame.

Note: All Spectra® breakers UL listed as HACR type.

All Spectra® breakers marked CE.

