

Medium Voltage Equipment Motor Control – Limitamp™ Frequently Requested Limitamp Renewal Parts CR194 and CR7160

Section 18

Limitamp Renewal Parts

Limitamp Type	Part	Description	CR194	CR7160	Product Number
	Arc Chute Assembly	Load Break Switch		•	204B4051BTG1
	Blade Assembly	Load Break Switch		•	204B4051BRG1
				N/A	9F60JD025
				N/A	9F60JD030
				N/A	9F60JD040
				N/A	9F60JD050
		9F60 Series		N/A	9F60JD065
				N/A	9F60JD080
				N/A	9F60JD100
				N/A	9F60JD125
				N/A	9F60JD150
				N/A	9F60JD200
			•	•	9F62HCB025
			•	•	9F62HCB030
			•	•	9F62HCB040
			•	•	9F62HCB050
		9F62 G.P. Series	•	•	9F62HCB065
		Equivalent Cont.	•	•	9F62DCB080
		Current Rating	•	•	9F62DCB100
			•	•	9F62DCB125
			•	•	9F62DCB150
			•	•	9F62DCB175
			•	•	9F62DCB200
			•	•	9F62HCB025
			•	•	9F62HCB030
			•	•	9F62HCB040
			•	•	9F62HCB050
		9F62 G.P. Series	•	•	9F62HCB065
		Equivalent XFMR Protection	•	•	9F62DCB080
			•	•	9F62DCB125
			•	•	9F62DCB150
			•	•	9F62DCB175
			•	•	9F62DCB200
		Air - Clip (5kV, 70A)	•	•	218A4291P2RB
		Air - Clip (5kV, 100A)	•	•	218A4291P3RB
		Air - Clip (5kV, 130A)	•	•	218A4291P4RB
		Air - Clip (5kV, 170A)	•	•	218A4291P6RB
		Air - Clip (5kV, 200A)	•	•	218A4291P9RB
		Air - Clip (5kV, 230A)	•	•	218A4291P12RB
		Air - Clip (5kV, 390A)	•	•	218A4291P18RB
		Air - Clip (5kV, 450A)	•	•	218A4291P24RB
		Air - Bolted (5kV, 70A)		•	218A4293P2RB
		Air - Bolted (5kV, 100A)		•	218A4293P3RB
		Air - Bolted (5kV, 130A)		•	218A4293P4RB
		Air - Bolted (5kV, 170A)		•	218A4293P6RB
		Air - Bolted (5kV, 200A)		•	218A4293P9RB
		Air - Bolted (5kV, 230A)		•	218A4293P12RB
		Air - Bolted (5kV, 390A)		•	218A4293P18RB
		Air - Bolted (5kV, 450A)		•	218A4293P24RB
		Vac. - Bolted (5kV, 70A)	•		55A212942P2RB
		Vac. - Bolted (5kV, 100A)	•		55A212942P3RB
		Vac. - Bolted (5kV, 130A)	•		55A212942P4RB
		Vac. - Bolted (5kV, 170A)	•		55A212942P6RB
		Vac. - Bolted (5kV, 200A)	•		55A212942P9RB
		Vac. - Bolted (5kV, 230A)	•		55A212942P12RB
		Vac. - Bolted (5kV, 390A)	•		55A212942P18RB
		Vac. - Bolted (5kV, 450A)	•		55A212942P24RB
		Vac. - Bolted - 800A (5kV, 425A)	•		55A213937P425B
		Vac. - Bolted - 800A (5kV, 550A)	•		55A213937P550B
		Vac. - Bolted - 800A (5kV, 630A)	•		55A213937P630B
		Vac. - Bolted - 800A (5kV, 800A)	•		55A213937P800B
		Air - Bolted (7.2kV, 70A)		•	218A4298P070
		Air - Bolted (7.2kV, 100A)		•	218A4298P100
		Air - Bolted (7.2kV, 180A)		•	218A4298P180
		Air - Bolted (7.2kV, 360A)		•	218A4298P360
		Vac. - Bolted (7.2kV, 70A)	•		55A212943P70
		Vac. - Bolted (7.2kV, 100A)	•		55A212943P100
		Vac. - Bolted (7.2kV, 180A)	•		55A212943P180
		Vac. - Bolted (7.2kV, 360A)	•		55A212943P360

