

NEMA Full Voltage Power Devices

NEMA Rated Full Voltage Contactors

CR305, CR385 Magnetic Contactors

Three-phase, Three-Pole
 Nonreversing, Open, NEMA Type 1, 3R, 12, 4/4X
 NEMA Sizes 00-9
 600 Volts Maximum 50/60 Hertz

GE Fastrac Program items are printed in red type.

Three-Pole:

List price includes holding contact (normally open) and pressure terminals for the line and load connections on NEMA Sizes 0-8 in Types 1, 3R, 12 and 4/4X enclosure, and Open Type NEMA Sizes 00-5. Open Type, NEMA Sizes 6-8 are supplied with bus bar type connections only. However, pressure box terminals are available, if required, and can be ordered by description, using the terminology: "Similar to (a listed product number) except with pressure box terminals." All NEMA Size 9 contactor forms are furnished with bus bar type connections only as standard.

CR305, Three-Phase, 3-Pole Magnetic Contactors NEMA sizes 00-6

NEMA Size	Continuous Ampere Rating ¹		Voltage @ 60 Hz	Horsepower	Open Type		NEMA Type 1		NEMA Type 3R		NEMA Type 12		NEMA Type 4/4X	
	Enclosed	Open			Product Number CR305	List Price GO-10G	Product Number CR305	List Price GO-10G	Product Number CR305	List Price GO-10G	Product Number CR305	List Price GO-10G	Product Number CR305	List Price GO-10G
00	9A	10A	115-120	—	A002	\$138.00	A102	\$150.00	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0
00	9A	10A	200-208	1 1/2	A023	\$138.00	A123	\$150.00	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0
00	9A	10A	230-240	1 1/2	A003	\$138.00	A103	\$150.00	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0
00	9A	10A	460-480	2	A004	\$138.00	A104	\$150.00	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0
00	9A	10A	575-600	2	A005	\$138.00	A105	\$150.00	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0
0	18A	20A	115-120	—	B002	\$174.00	B102	\$186.00	B602	\$258.00	B202	\$258.00	B402	\$396.00
0	18A	20A	200-208	3	B023	\$174.00	B123	\$186.00	B623	\$258.00	B223	\$258.00	B423	\$396.00
0	18A	20A	230-240	3	B003	\$174.00	B103	\$186.00	B603	\$258.00	B203	\$258.00	B403	\$396.00
0	18A	20A	460-480	5	B004	\$174.00	B104	\$186.00	B604	\$258.00	B204	\$258.00	B404	\$396.00
0	18A	20A	575-600	5	B005	\$174.00	B105	\$186.00	B605	\$258.00	B205	\$258.00	B405	\$396.00
1	27A	30A	115-120	—	C002	\$204.00	C102	\$216.00	C602	\$288.00	C202	\$288.00	C402	\$432.00
1	27A	30A	200-208	7 1/2	C023	\$204.00	C123	\$216.00	C623	\$288.00	C223	\$288.00	C423	\$432.00
1	27A	30A	230-240	7 1/2	C003	\$204.00	C103	\$216.00	C603	\$288.00	C203	\$288.00	C403	\$432.00
1	27A	30A	460-480	10	C004	\$204.00	C104	\$216.00	C604	\$288.00	C204	\$288.00	C404	\$432.00
1	27A	30A	575-600	10	C005	\$204.00	C105	\$216.00	C605	\$288.00	C205	\$288.00	C405	\$432.00
2	45A	50A	115-120	—	D002	\$372.00	D102	\$432.00	D602	\$564.00	D202	\$564.00	D402	\$864.00
2	45A	50A	200-208	10	D023	\$372.00	D123	\$432.00	D623	\$564.00	D223	\$564.00	D423	\$864.00
2	45A	50A	230-240	15	D003	\$372.00	D103	\$432.00	D603	\$564.00	D203	\$564.00	D403	\$864.00
2	45A	50A	460-480	25	D004	\$372.00	D104	\$432.00	D604	\$564.00	D204	\$564.00	D404	\$864.00
2	45A	50A	575-600	25	D005	\$372.00	D105	\$432.00	D605	\$564.00	D205	\$564.00	D405	\$864.00
3	90A	100A	115-120	—	E002	\$600.00	E102	\$720.00	E602	\$876.00	E202	\$876.00	E402	\$1332.00
3	90A	100A	200-208	25	E023	\$600.00	E123	\$720.00	E623	\$876.00	E223	\$876.00	E423	\$1332.00
3	90A	100A	230-240	30	E003	\$600.00	E103	\$720.00	E603	\$876.00	E203	\$876.00	E403	\$1332.00
3	90A	100A	460-480	50	E004	\$600.00	E104	\$720.00	E604	\$876.00	E204	\$876.00	E404	\$1332.00
3	90A	100A	575-600	50	E005	\$600.00	E105	\$720.00	E605	\$876.00	E205	\$876.00	E405	\$1332.00
4	135A	150A	115-120	—	F002	\$1440.00	F102	\$1692.00	F602	\$2208.00	F202	\$2208.00	F402	\$2736.00
4	135A	150A	200-208	40	F023	\$1440.00	F123	\$1692.00	F623	\$2208.00	F223	\$2208.00	F423	\$2736.00
4	135A	150A	230-240	50	F003	\$1440.00	F103	\$1692.00	F603	\$2208.00	F203	\$2208.00	F403	\$2736.00
4	135A	150A	460-480	100	F004	\$1440.00	F104	\$1692.00	F604	\$2208.00	F204	\$2208.00	F404	\$2736.00
4	135A	150A	575-600	100	F005	\$1440.00	F105	\$1692.00	F605	\$2208.00	F205	\$2208.00	F405	\$2736.00
5	270A	300A	115-120	—	G002	\$3138.00	G102	\$3600.00	G602	\$4920.00	G202	\$4920.00	G402	\$4920.00
5	270A	300A	200-208	75	G023	\$3138.00	G123	\$3600.00	G623	\$4920.00	G223	\$4920.00	G423	\$4920.00
5	270A	300A	230-240	100	G003	\$3138.00	G103	\$3600.00	G603	\$4920.00	G203	\$4920.00	G403	\$4920.00
5	270A	300A	460-480	200	G004	\$3138.00	G104	\$3600.00	G604	\$4920.00	G204	\$4920.00	G404	\$4920.00
5	270A	300A	575-600	200	G005	\$3138.00	G105	\$3600.00	G605	\$4920.00	G205	\$4920.00	G405	\$4920.00
6	540A	600A	115-120	—	HH002	\$8568.00	HH102AA2A	\$10602.00	HH602AA2A	\$12222.00	HH202AA2A	\$12222.00	HH402AA2A	\$13602.00
6	540A	600A	200-208	150	HH023	\$8568.00	HH123AA2A	\$10602.00	HH623AA2A	\$12222.00	HH223AA2A	\$12222.00	HH423AA2A	\$13602.00
6	540A	600A	230-240	200	HH003	\$8568.00	HH103AA2A	\$10602.00	HH603AA2A	\$12222.00	HH203AA2A	\$12222.00	HH403AA2A	\$13602.00
6	540A	600A	460-480	400	HH004	\$8568.00	HH104AA2A	\$10602.00	HH604AA2A	\$12222.00	HH204AA2A	\$12222.00	HH404AA2A	\$13602.00
6	540A	600A	575-600	400	HH005	\$8568.00	HH105AA2A	\$10602.00	HH605AA2A	\$12222.00	HH205AA2A	\$12222.00	HH405AA2A	\$13602.00

CR385, Three-Phase, 3-Pole Magnetic Contactors NEMA sizes 7-9

¹Motor full-load current should not exceed continuous ampere rating of contactor.

NEMA Size	Continuous Ampere Rating ¹	Control Motor Voltage	Horsepower	Circuit Voltage	Open Type	
					Product Number CR385	List Price GO-10G
7	900A	N/A	—	115	J002AA1A	\$12228.00
7	900A	220-240	300	230	J003AA1A	\$12228.00
7	900A	440-480	600	460	J004AA1A	\$12228.00
7	900A	550-600	600	575	J005AA1A	\$12228.00
8	1350A	N/A	—	115	K002AA1A	\$18876.00
8	1350A	220-240	450	230	K003AA1A	\$18876.00
8	1350A	440-480	900	460	K004AA1A	\$18876.00
8	1350A	550-600	900	575	K005AA1A	\$18876.00
9	2500A	N/A	—	115	L002AA1A	\$25410.00
9	2500A	220-240	800	230	L003AA1A	\$25410.00
9	2500A	440-480	1600	460	L004AA1A	\$25410.00
9	2500A	550-600	1600	575	L005AA1A	\$25410.00

Enclosure Descriptions: See Section 13

