



RS 2-xxx

DESCRIPTION

These switches are designed for installation in mounting straps with cover plates or for snap in panel mounting (0.76" x 1.28"). The line includes 2-button switches with 2 normally open 3 AMP 28 VAC contacts providing a single-pole double-throw configuration certified by CSA.

These are available in 3 types:

1. Unlighted
2. Locator with 0.03 AMP 28 VAC locator lamp in "ON" button
3. Pilot with 0.04 AMP 28 VAC pilot lamp in "ON" button

Each switch is provided with Quick Disconnect terminals 0.187" wide by 0.020".

Operating

Environment 0-55 Degrees C (32-131F)
0-95% RH, Non Condensing
Non Corrosive Atmosphere

SPECIFICATIONS

Description Specifier Series Low Voltage Switches

Switches

Catalog #	Description	Color (Black Trim)
RS 2-32*	Unlighted	Ivory
RS 2-37*	Unlighted	White
RS 2-39*	Unlighted	Grey
RS 2-32L*	Locator	Ivory
RS 2-37L*	Locator	White
RS 2-39L*	Locator	Grey
RS 2-32P*	Pilot	Ivory with red
RS 2-37P*	Pilot	White with red
RS 2-38P	Pilot	Opaque red
RS 2-38PA	Pilot	Clear red
RS 2-39P*	Pilot	Grey with red
RS 2-32RL	Raise/Lower	Ivory with red arrows
RS 2-37RL	Raise/Lower	White with red arrows
RS 2-39RL	Raise/Lower	Grey with red arrows

* Add "K" after catalog # for Key Switch

Accessories

Catalog #	Description	Color
RA 2-32	Blank	Ivory
RA 2-37	Blank	White
RA 2-39	Blank	Grey
RA 2-QC	Extra Female Quick Disconnect Terminals (Insulated)	

Job Name: _____	Page: ____ of ____