

Definite Purpose Controls Full Voltage Contactors

CR353

Standard
Three Phase
2-pole and 3-pole
50A - 150A

Standard Forms

Standard CR353 contactors in the 50-120FLA ratings are supplied with box lug terminals. Power poles in the 50-90FLA size are supplied with two 1/4" quick connect terminals. Contactors in the 120-150FLA size include control power accessory screws on L1 and L2. Coils are provided with screw connections with a single 1/4" quick connect terminal on the 50 and 60 amp size and two 1/4" quick connect terminals on the 75 and 90 amp size.

For configurations not found below see page 4-11 for Factory Modified Forms.



CR353 Contactor

CR353 Standard (2-pole and 3-pole)

Inductive Amps	Resistive Amps	Locked Rotor Amps, 50/60 Hz @ 240V	Locked Rotor Amps, 50/60 Hz @ 480V	Locked Rotor Amps, 50/60 Hz @ 600V	No. of Poles	Product Number	List Price GO-10DP
50	62	300	250	200	2	CR353FE2B*1	\$121.00
50	62	300	250	200	3	CR353FE3B*1	\$134.00
60	75	360	300	240	2	CR353FF2B*1	\$141.00
60	75	360	300	240	3	CR353FF3B*1	\$157.00
75	90	450	375	300	2	CR353EG2B*1	\$203.00
75	90	450	375	300	3	CR353EG3B*1	\$225.00
90	90	540	450	360	2	CR353EH2B*1	\$290.00
90	90	540	450	360	3	CR353EH3B*1	\$322.00
120	120	720	600	480	2	CR353GJ2A*1	\$423.00
120	120	720	600	480	3	CR353GJ3A*1	\$460.00
150	150	900	750	600	2	CR353GK2A*1	\$816.00
150	150	900	750	600	3	CR353GK3A*1	\$900.00

(Replace * in product number with appropriate coil digit.)

Coil Selection

CR353F, E, G Coil Selection

AC Coils

CR353F, E Coil Voltage		CR353G Coil Voltage		Product No. Digit
60 Hz	50 Hz	60 Hz	50 Hz	
24	24	—	—	H
110-120	110-120	115-120	110	A
208-240	208-240	230-240	220	B
277	—	277	—	F
460-480	440	460-480	440	C
575-600	550	575-600	550	D

DC Coils

CR353F Coil Voltage	CR353E Coil Voltage	Product No. Digit	List Price Adder GO-10DP
12	12	P	\$36.00
24-28	24-28	R	\$36.00
110-125	110-125	S	\$36.00
—	48	T	\$36.00

