

# Molded Case Circuit Breakers

## Q-Line Circuit Breakers

Bolt-on Circuit Breakers  
240V Class

### THHQB 120/240 Vac

| # of Poles | Ampere Rating | Wire Range <sup>1</sup> | 120/240 Vac Interrupting Rating | Product Number         |
|------------|---------------|-------------------------|---------------------------------|------------------------|
| 1          | 15            | 14-8 Cu/12-8 Al         | 22kA                            | THHQB1115 <sup>2</sup> |
| 1          | 20            | 14-8 Cu/12-8 Al         | 22kA                            | THHQB1120 <sup>2</sup> |
| 1          | 25            | 14-8 Cu/12-8 Al         | 22kA                            | THHQB1125              |
| 1          | 30            | 14-8 Cu/12-8 Al         | 22kA                            | THHQB1130              |
| 1          | 35            | 8-3 Cu/8-3 Al           | 22kA                            | THHQB1135              |
| 1          | 40            | 8-3 Cu/8-3 Al           | 22kA                            | THHQB1140              |
| 1          | 45            | 8-3 Cu/8-3 Al           | 22kA                            | THHQB1145              |
| 1          | 50            | 8-3 Cu/8-3 Al           | 22kA                            | THHQB1150              |
| 1          | 60            | 8-3 Cu/8-3 Al           | 22kA                            | THHQB1160              |
| 1          | 70            | 6-1/0 Cu/4-1/0 Al       | 22kA                            | THHQB1170              |

### THQB/THHQB 120/240 Vac, Low Magnetic Pickup

| # of Poles | Ampere Rating | Wire Range <sup>1</sup> | 120/240 Vac Interrupting Rating | Product Number          |
|------------|---------------|-------------------------|---------------------------------|-------------------------|
| 1          | 15            | 14-8 Cu/12-8 Al         | 10 kA                           | THQB1115LM <sup>2</sup> |
| 1          | 20            | 14-8 Cu/12-8 Al         | 10 kA                           | THQB1120LM <sup>2</sup> |
| 1          | 15            | 14-8 Cu/12-8 Al         | 22 kA                           | THHQB1115LM             |
| 1          | 20            | 14-8 Cu/12-8 Al         | 22 kA                           | THHQB1120LM             |
| 2          | 15            | 14-8 Cu/12-8 Al         | 10 kA                           | THQB2115LM              |
| 2          | 20            | 14-8 Cu/12-8 Al         | 10 kA                           | THQB2120LM              |
| 2          | 15            | 14-8 Cu/12-8 Al         | 22 kA                           | THHQB2115LM             |
| 2          | 20            | 14-8 Cu/12-8 Al         | 22 kA                           | THHQB2120LM             |

### THHQB 120/240 Vac, Internal Common Trip

| # of Poles | Ampere Rating | Wire Range <sup>1</sup> | 120/240 Vac Interrupting Rating | Product Number |
|------------|---------------|-------------------------|---------------------------------|----------------|
| 2          | 15            | 14-8 Cu/12-8 Al         | 22kA                            | THHQB2115      |
| 2          | 20            | 14-8 Cu/12-8 Al         | 22kA                            | THHQB2120      |
| 2          | 25            | 14-8 Cu/12-8 Al         | 22kA                            | THHQB2125      |
| 2          | 30            | 14-8 Cu/12-8 Al         | 22kA                            | THHQB2130      |
| 2          | 35            | 8-3 Cu/8-3 Al           | 22kA                            | THHQB2135      |
| 2          | 40            | 8-3 Cu/8-3 Al           | 22kA                            | THHQB2140      |
| 2          | 45            | 8-3 Cu/8-3 Al           | 22kA                            | THHQB2145      |
| 2          | 50            | 8-3 Cu/8-3 Al           | 22kA                            | THHQB2150      |
| 2          | 60            | 8-3 Cu/8-3 Al           | 22kA                            | THHQB2160      |
| 2          | 70            | 6-1/0 Cu/4-1/0 Al       | 22kA                            | THHQB2170      |
| 2          | 80            | 6-1/0 Cu/4-1/0 Al       | 22kA                            | THHQB2180      |
| 2          | 90            | 6-1/0 Cu/4-1/0 Al       | 22kA                            | THHQB2190      |
| 2          | 100           | 6-1/0 Cu/4-1/0 Al       | 22kA                            | THHQB21100     |



THHQB2115

### THHQB 240 Vac, Internal Common Trip

| # of Poles | Ampere Rating | Wire Range <sup>1</sup> | 240 Vac Interrupting Rating | Product Number |
|------------|---------------|-------------------------|-----------------------------|----------------|
| 2          | 15            | 14-8 Cu/12-8 Al         | 22kA                        | THHQB22015     |
| 2          | 20            | 14-8 Cu/12-8 Al         | 22kA                        | THHQB22020     |
| 2          | 25            | 14-8 Cu/12-8 Al         | 22kA                        | THHQB22025     |
| 2          | 30            | 14-8 Cu/12-8 Al         | 22kA                        | THHQB22030     |
| 2          | 35            | 8-3 Cu/8-3 Al           | 22kA                        | THHQB22035     |
| 2          | 40            | 8-3 Cu/8-3 Al           | 22kA                        | THHQB22040     |
| 2          | 45            | 8-3 Cu/8-3 Al           | 22kA                        | THHQB22045     |
| 2          | 50            | 8-3 Cu/8-3 Al           | 22kA                        | THHQB22050     |
| 2          | 60            | 8-3 Cu/8-3 Al           | 22kA                        | THHQB22060     |
| 2          | 70            | 6-1/0 Cu/4-1/0 Al       | 22kA                        | THHQB22070     |
| 2          | 80            | 6-1/0 Cu/4-1/0 Al       | 22kA                        | THHQB22080     |
| 2          | 90            | 6-1/0 Cu/4-1/0 Al       | 22kA                        | THHQB22090     |
| 2          | 100           | 6-1/0 Cu/4-1/0 Al       | 22kA                        | THHQB22100     |
| 3          | 15            | 14-8 Cu/12-8 Al         | 22kA                        | THHQB32015     |
| 3          | 20            | 14-8 Cu/12-8 Al         | 22kA                        | THHQB32020     |
| 3          | 25            | 14-8 Cu/12-8 Al         | 22kA                        | THHQB32025     |
| 3          | 30            | 14-8 Cu/12-8 Al         | 22kA                        | THHQB32030     |
| 3          | 35            | 8-3 Cu/8-3 Al           | 22kA                        | THHQB32035     |
| 3          | 40            | 8-3 Cu/8-3 Al           | 22kA                        | THHQB32040     |
| 3          | 45            | 8-3 Cu/8-3 Al           | 22kA                        | THHQB32045     |
| 3          | 50            | 8-3 Cu/8-3 Al           | 22kA                        | THHQB32050     |
| 3          | 60            | 8-3 Cu/8-3 Al           | 22kA                        | THHQB32060     |
| 3          | 70            | 6-1/0 Cu/4-1/0 Al       | 22kA                        | THHQB32070     |
| 3          | 80            | 6-1/0 Cu/4-1/0 Al       | 22kA                        | THHQB32080     |
| 3          | 90            | 6-1/0 Cu/4-1/0 Al       | 22kA                        | THHQB32090     |
| 3          | 100           | 6-1/0 Cu/4-1/0 Al       | 22kA                        | THHQB32100     |

<sup>1</sup>Solid or stranded for 14-10 AWG.

<sup>2</sup>UL listed as SWD (switching duty) rated. Suitable for switching 120 Vac fluorescent lighting loads.

UL listed HACR (heating, air conditioning and refrigeration).

