



RS 2-xxx

DESCRIPTION

These switches are designed for installation in mounting straps with cover plates or for snap in panel mounting (0.76" x 1.28"). The line includes 2-button switches with 2 normally open 3 AMP 28 VAC contacts providing a single-pole double-throw configuration certified by CSA.

These are available in 3 types:

1. Unlighted
2. Locator with 0.03 AMP 28 VAC locator lamp in "ON" button
3. Pilot with 0.04 AMP 28 VAC pilot lamp in "ON" button

Each switch is provided with Quick Disconnect terminals 0.187" wide by 0.020".

Operating

Environment 0-55 Degrees C (32-131F)
0-95% RH, Non Condensing
Non Corrosive Atmosphere

SPECIFICATIONS

Description Specifier Series Low Voltage Switches

Switches

| Catalog # | Description | Color (Black Trim) |
|-----------|-------------|-----------------------|
| RS 2-32* | Unlighted | Ivory |
| RS 2-37* | Unlighted | White |
| RS 2-39* | Unlighted | Grey |
| RS 2-32L* | Locator | Ivory |
| RS 2-37L* | Locator | White |
| RS 2-39L* | Locator | Grey |
| RS 2-32P* | Pilot | Ivory with red |
| RS 2-37P* | Pilot | White with red |
| RS 2-38P | Pilot | Opaque red |
| RS 2-38PA | Pilot | Clear red |
| RS 2-39P* | Pilot | Grey with red |
| RS 2-32RL | Raise/Lower | Ivory with red arrows |
| RS 2-37RL | Raise/Lower | White with red arrows |
| RS 2-39RL | Raise/Lower | Grey with red arrows |

* Add "K" after catalog # for Key Switch

Accessories

| Catalog # | Description | Color |
|-----------|---|-------|
| RA 2-32 | Blank | Ivory |
| RA 2-37 | Blank | White |
| RA 2-39 | Blank | Grey |
| RA 2-QC | Extra Female Quick Disconnect Terminals (Insulated) | |

Job Name: _____ Page: ____ of ____