



Catalog No. 9T21B1037G02

Description: ENCLOSED MEDIUM POWER TRANSFORMERS

UPC No 783173004692

Products > Transformers > Dry Type, Encapsulated, Enclosed > Buck Boost

These GE transformers feature encapsulated core and coils in a NEMA 3R non-ventilated weatherproof enclosure

- UL Listed
- C-UL Listed
- Knockouts provided on back and bottom
- High grade silicon steel core
- Mounting holes on side for easy access
- Wiring compartment includes ground stud

Descriptors

Category	Buck Boost
GO Schedule	T8

Specifications

Phase	1
PriVoltage	120x240
SecVoltage	12/24
KVA	5.0 KVA
Coil Material	AL
TempRise	115.0 °C
ElecShield	N
SubType	BUCK BOOST
Frequency	60 Hz
FrameSize	16350
Net Weight	103
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
Net Weight	103
GSA Compliance	No

Classifications

UL	Yes
cUL	Yes
CE	No

Dimensions

Width	10.6 in
Depth	11.0 in
Height	14.5 in

Publications

Title	Publication No.	Publication Type
Transformer Outline Drawing Outline drawing in .pdf format.	303B923AAP005	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.