



### Catalog No. 9T21B1040G02

Description: ENCLOSED MEDIUM POWER TRANSFORMERS

UPC No 783173004524

Products > Transformers > Dry Type, Encapsulated, Enclosed > Buck Boost

These GE transformers feature encapsulated core and coils in a NEMA 3R non-ventilated weatherproof enclosure

- UL Listed
- C-UL Listed
- Knockouts provided on back and bottom
- High grade silicon steel core
- Mounting holes on side for easy access
- Wiring compartment includes ground stud

#### Descriptors

Category	Buck Boost
GO Schedule	T8

#### Specifications

Phase	1
PriVoltage	120x240
SecVoltage	16/32
KVA	5.0 KVA
Coil Material	AL
TempRise	115.0 °C
ElecShield	N
SubType	BUCK BOOST
Frequency	60 Hz
FrameSize	16400
Net Weight	115
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
Net Weight	115
GSA Compliance	Yes

#### Classifications

UL	Yes
cUL	Yes
CE	No

#### Dimensions

Width	10.6 in
Depth	11.0 in
Height	14.5 in

## Publications

Title	Publication No.	Publication Type
<a href="#">Transformer Outline Drawing</a> Outline drawing in .pdf format.	303B923AAP005	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.