



## Catalog No. 9T21B1046G02

**Description: ENCLOSED MEDIUM POWER TRANSFORMERS**

**UPC No 783173006986**

**Products > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

These GE transformers feature encapsulated core and coils in a NEMA 3R non-ventilated weatherproof enclosure

- UL Listed
- C-UL Listed
- Knockouts provided on back and bottom
- High grade silicon steel core
- Mounting holes on side for easy access
- Wiring compartment includes ground stud

### Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T7

### Specifications

Phase	1
PriVoltage	277
SecVoltage	120/240
KVA	5.0 KVA
Coil Material	AL
TempRise	115.0 °C
ElecShield	N
SubType	Standard
Frequency	60 Hz
FrameSize	16350
Net Weight	103
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
Net Weight	103
Taps	(-2 5.1%)
GSA Compliance	No

### Classifications

UL	Yes
cUL	Yes
CE	No

### Dimensions

Width	10.6 in
Depth	11.0 in
Height	14.5 in

## Dimensions

Width	10.6 in
Depth	11.0 in
Height	14.5 in

## Publications

Title	Publication No.	Publication Type
<a href="#">Transformer Outline Drawing</a> Outline drawing in .pdf format.	303B923AAP005	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.