



Catalog No. 9T21B9104

Description: 25KVA AL 240X480 120/240 ENCP SLTD

UPC No 783173002261

Products > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

These GE transformers feature encapsulated core and coils in a NEMA 3R non-ventilated weatherproof enclosure

- UL Listed
- C-UL Listed
- Knockouts provided on back and bottom
- High grade silicon steel core
- Mounting holes on side for easy access
- Wiring compartment includes ground stud

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T7

Specifications

Phase	1
PriVoltage	240x480
SecVoltage	120/240
KVA	25.0 KVA
Coil Material	AL
TempRise	115.0 °C
ElecShield	N
SubType	Standard
Frequency	60 Hz
Impedance	2.4 %
FrameSize	50500
Net Weight	388 lb
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
Net Weight	388 lb
GSA Compliance	No

Classifications

UL	Yes
cUL	Yes
CE	No

Dimensions

Width	16.8 in
Depth	16.0 in
Height	20.9 in

Dimensions

Width	16.8 in
Depth	16.0 in
Height	20.9 in

Publications

Title	Publication No.	Publication Type
Transformer Outline Drawing Outline drawing in .pdf format.	303B923AAP025	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.