



## Catalog No. 9T21B9114

Description: 25KVA AL 600(-2 5%) 120/240 ENCPSLT

UPC No 783173002223

Products > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

These GE transformers feature encapsulated core and coils in a NEMA 3R non-ventilated weatherproof enclosure

- UL Listed
- C-UL Listed
- Knockouts provided on back and bottom
- High grade silicon steel core
- Mounting holes on side for easy access
- Wiring compartment includes ground stud

### Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T7

### Specifications

Phase	1
PriVoltage	600
SecVoltage	120/240
KVA	25.0 KVA
Coil Material	AL
TempRise	115.0 °C
ElecShield	N
SubType	Standard
Frequency	60 Hz
Impedance	2.4 %
FrameSize	50500
Net Weight	388 lb
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
Net Weight	388 lb
Taps	(-2 5.0%)
GSA Compliance	No

### Classifications

UL	Yes
cUL	Yes
CE	No

### Dimensions

Width	16.8 in
Depth	16.0 in

## Dimensions

Height

20.9 in

## Publications

Title	Publication No.	Publication Type
<a href="#">Transformer Outline Drawing</a> Outline drawing in .pdf format.	303B923AAP025	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.