



## Catalog No. 9T21C3319

Description: TFMR 15KVA 240X480-120/240 ST CU 11

UPC No 783173011997

Products > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

These GE transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure

- UL Listed
- C-UL Listed
- Knockouts provided on back and bottom
- High grade silicon steel core
- Mounting holes on side for easy access
- Wiring compartment includes ground stud

### Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T7

### Specifications

Phase	1
PriVoltage	240x480
SecVoltage	120/240
KVA	15.0 KVA
Coil Material	CU
TempRise	115.0 °C
ElecShield	N
SubType	Standard
Frequency	60 Hz
Impedance	0.00 %
FrameSize	19500
Net Weight	267
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
EnergyEfficiency	None
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	267
Sound	Std
GSA Compliance	No

### Classifications

UL	Yes
cUL	Yes
CE	No

**Dimensions**

Width	12.5 in
Depth	12.5 in
Height	17.1 in

## Publications

Title	Publication No.	Publication Type
<a href="#">Transformer Outline Drawing</a> Outline drawing in .pdf format.	303B923AAP015	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.