



## Catalog No. 9T51B0125

Description: TRANSFORMER

UPC No 783173008638

Products > Transformers > Dry Type, Encapsulated, Enclosed > Buck Boost

These GE transformers feature an encapsulated core and coil in a NEMA 3R non-ventilated weatherproof enclosure.

- UL Listed
- C-UL Listed
- Knockouts provided on back and bottom
- High grade silicon steel core
- Mounting holes on side for easy access

Wiring compartment includes ground stud

### Descriptors

Category	Buck Boost
GO Schedule	T6

### Specifications

Phase	1
PriVoltage	120x240
SecVoltage	16/32
KVA	0.15 KVA
Coil Material	CU
TempRise	55.0 °C
ElecShield	N
SubType	BUCK BOOST
Frequency	60 Hz
FrameSize	8175
Net Weight	10
TempClass	105.0 °C
AmbTemp	40.0 °C
InsulSys	CLASSA
EnergyEfficiency	None
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	10
Sound	Std
GSA Compliance	No

### Classifications

UL	Yes
cUL	Yes
CE	No

## Dimensions

Width	6.1 in
Depth	4.2 in
Height	7.4 in

## Publications

Title	Publication No.	Publication Type
<a href="#">Transformer Outline Drawing</a> Outline drawing in .pdf format.	303B920AAP002	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.