



## Catalog No. 9T51B0190

Description: ENCLOSED SMALL POWER TRANSFORMERS

UPC No 783173010518

Products > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

These GE transformers feature an encapsulated core and coil in a NEMA 3R non-ventilated weatherproof enclosure.

- UL Listed
- C-UL Listed
- Knockouts provided on back and bottom
- High grade silicon steel core
- Mounting holes on side for easy access

Wiring compartment includes ground stud

### Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

### Specifications

Phase	1
PriVoltage	277
SecVoltage	120/240
KVA	1.00 KVA
Coil Material	CU
TempRise	100.0 °C
ElecShield	N
SubType	Standard
Frequency	60 Hz
FrameSize	12275
Net Weight	30
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
EnergyEfficiency	None
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	30
Sound	Std
Taps	(-2 5.1%)
GSA Compliance	Yes

### Classifications

UL	Yes
cUL	Yes
CE	No

## Dimensions

Width	7.9 in
Depth	5.5 in
Height	9.6 in

## Publications

Title	Publication No.	Publication Type
<a href="#">Transformer Outline Drawing</a> Outline drawing in .pdf format.	303B920AAP004	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.