



## Catalog No. 9T51B0213

Description: ENCLOSED SMALL POWER TRANSFORMERS

UPC No 783173036839

Products > Transformers > Dry Type, Encapsulated, Enclosed > Buck Boost

These GE transformers feature an encapsulated core and coil in a NEMA 3R non-ventilated weatherproof enclosure.

- UL Listed
- C-UL Listed
- Knockouts provided on back and bottom
- High grade silicon steel core
- Mounting holes on side for easy access

Wiring compartment includes ground stud

### Descriptors

Category	Buck Boost
GO Schedule	T6

### Specifications

Phase	1
PriVoltage	240x480
SecVoltage	24/48
KVA	3.0 KVA
Coil Material	CU
TempRise	115.0 °C
ElecShield	N
SubType	BUCK BOOST
Frequency	60 Hz
FrameSize	14350
Net Weight	55
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
EnergyEfficiency	None
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	55
Sound	Std
GSA Compliance	No

### Classifications

UL	Yes
cUL	Yes
CE	No

## Dimensions

Width	9.4 in
Depth	6.7 in
Height	11.1 in

## Publications

Title	Publication No.	Publication Type
<a href="#">Transformer Outline Drawing</a> Outline drawing in .pdf format.	303B920AAP005	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.