



Catalog No. 9T51B0502

Description: .050KVA 50/60HZ 240-480V 120/240V

UPC No 783173011218

Products > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

These GE transformers feature an encapsulated core and coil in a NEMA 3R non-ventilated weatherproof enclosure.

- UL Listed
- C-UL Listed
- Knockouts provided on back and bottom
- High grade silicon steel core
- Mounting holes on side for easy access

Wiring compartment includes ground stud

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

Specifications

Phase	1
PriVoltage	240x480
SecVoltage	120/240
KVA	0.05 KVA
Coil Material	CU
TempRise	55.0 °C
ElecShield	N
SubType	Standard
Frequency	50 Hz
FrameSize	6100
Net Weight	6
TempClass	105.0 °C
AmbTemp	40.0 °C
InsulSys	CLASSA
EnergyEfficiency	None
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	6
Sound	Std
GSA Compliance	No

Classifications

UL	Yes
cUL	Yes
CE	No

Dimensions

Width	5.1 in
Depth	3.2 in
Height	6.4 in

Publications

Title	Publication No.	Publication Type
Transformer Outline Drawing Outline drawing in .pdf format.	303B920AAP001	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.