



Actual

**Catalog Number:** 2B20BB  
**Product ID:** 7TAH006160R0007  
**UPC Number:** 78378640002  
**Status:** Active

Copper Type 2B - Two-Bolt Connector without Spacer for Wire Range Main: 2 - 2/0 Str. Tap: 8 Sol. - 2/0 Str. , Bolt Size 1/2

- Castings and bolts of high-strength copper alloy. Removable cap.
- UL 486A listed for copper conductor only.

### North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Two-Bolt Connector
Special Features	Castings and bolts of high-strength copper alloy. Removable cap.
Standard	UL E9809
Material	Copper
Conductor Range (Main/Primary)	2 - 2/0 Str.
Conductor Range (Tap/Secondary)	8 Sol. - 2/0 Str.
Bolt Size	42737

### European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Copper

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	5x3.37x6.5
Outer Quantity	250
Outer Dimensions (inches)	19x10.75x7.75
Weight Uom	20.81 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)