



Actual

Catalog Number: AK 600 N
Product ID: 7TAA261360R0054
UPC Number: 78378669266
Status: Active

Aluminum Lay-In Transformer Spade Connectors - AK Series, cable range 2-600, outlets 1

North American Specifications (UNSPSC)

UNSPSC	39121407 Terminal strips
IGCC	4538 Terminal strips
Brand Name	Homac
Type	Transformer Connector
Special Features	The Slide-out Keeper Minimizes the hassle and hazards of forcing cables into closed ports. Require only a cable stripper and Allen hex wrench - no crimping tools or dies or other special tools needed for installation. Transformer changes require only the connector to be unbolted from the spade - no need to disconnect all the conductors, as with compression systems. Dual rated to use with Aluminum or Copper. Double Set Screws maximize contact area and mechanical characteristics. Ball-bottom screws ensure even force distribution in the cable/connector interface.
Application	Lay-In Transformer Spade Connector
Number Of Terminals	1
Wire Size	2 to 600
Material	Aluminum
Connection	Mechanical
Size	Body is 2.750 inch long, 1.642 inch wide, 2.108 inch high.

Packaging

Outer Quantity	10
Outer Dimensions (inches)	7.5x6x6.5
Weight Uom	1.09 lbs. Each

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com