



Representative

Catalog Number: CF1010-1
Product ID: 7TAA267230R0000
UPC Number: 78378609336
Status: Active

Copper H-Type Compression Connector Main: 1/0, 1, 2 Stranded Copper, Tap: 1/0, 1, 2 Stranded Copper

North American Specifications (UNSPSC)

UNSPSC	39121448 Wire or cable compression connector
IGCC	4668 Wire or cable compression connector
Brand Name	Blackburn
Type	H-Type Compression Connector
Special Features	Efficient Design Requires Less Crimping Force. Full Length Tab makes Installation Easy. Installs with Standard Compression Tools and Dies. RUS Accepted.
Conductor Range	Tap .292-.373 inch
Material	Electrolytic Copper
Conductor Type	Crimp
Conductor Range (Main/Primary)	.292-.373 inch
Bolt Size	N/A
Mounting Hole Spacing	N/A

Packaging

Inner Quantity	100
Inner Dimensions (inches)	7.4x5.2x4.9
Outer Quantity	300
Outer Dimensions (inches)	15x8x5.9
Weight Uom	10 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000520

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com