

# Pilot and Signaling Devices

## Heavy-Duty 22.5 mm Watertight/Oiltight Push Buttons

### C-2000

Standard

Non-Illuminated

600 VAC Max., 300 VDC Max.

10 Amps Continuous AC, 2.5 Amps Continuous DC

#### Selection Process

Select operator + Select contact block(s) + Select nameplate, if required, = Complete Unit  
below from page 9-93 from pages 9-95 to 9-97



#### Operators

Standard Push Button Type	Operator Style	Product Number	List Price GO-10GC
Flush	Round Polished Chrome	P9CPN*G	\$8.50
Flush	Round Satin Chrome	P9MPN*G	\$8.50
Flush	Round Engineered Plastic	P9XPN*G	\$8.50
Flush	Square Engineered Plastic	P9SPN*G	\$8.50
Extended	Round Polished Chrome	P9CPN*S	\$8.50
Extended	Round Satin Chrome	P9MPN*S	\$8.50
Extended	Round Engineered Plastic	P9XPN*S	\$8.50
Extended	Square Engineered Plastic	P9SPN*S	\$8.50
Recessed	Round Polished Chrome	P9CPN*E	\$8.50
Recessed	Round Satin Chrome	P9MPN*E	\$8.50

Replace asterisk (\*) in product number with color code from table below

#### \*Colors

Colors	Black	Red	Green	Yellow	Blue	White	Brown	Gray	No Cap <sup>1</sup>
*Color code	N	R	V	G	L	B	M	H	0

<sup>1</sup>When ordering operator with no cap, deduct \$1.00 from List Price.

Color caps are listed on page 9-103.



Recessed



Flush



Extended



Square Engineered Plastic

