

Contractor Kits

Load Center & Circuit Breakers Included
 Factory Installed Main Breaker & Equipment Ground Kit – Indoor Type 1 Enclosure
 Single Phase, Three-Wire, 120/240Vac

| Kit Includes | | | | | | Load Center | Equipment Ground Kit Installed | Kit Catalog Number | List Price, GO-137E | |
|--------------------|--------|--------|--------|--------|------------|-------------|--------------------------------|--------------------|---------------------|-------|
| Circuit Breakers | | | | | | | | | | |
| 1" THQL Breakers | 15A 1P | 15A 2P | 20A 2P | 30A 2P | 40A 2P | | | | | |
| | | 10 | 3 | — | 1 | 1 | TMC2410CCA | (2) TGK24 | TMC2410CCA2K | \$855 |
| | | 10 | 3 | — | 1 | 1 | TMC3210CCA | (2) TGK42 | TMC3210CCA2K | 870 |
| | | 10 | 3 | — | 1 | 1 | TMC3220CCA | (2) TGK12 | TMC3220CCA2K | 1215 |
| | | 10 | 3 | — | 1 | 1 | TMC4020CCA | (2) TGK32 | TMC4020CCA2K | 1290 |
| | | 14 | 2 | 3 | 2 | 1 | TMC4020CCA | (2) TGK24 | TMC4020CCA4K | 1540 |
| 1/2" THQP Breakers | 10 | 3 | — | 1 | 1 | TMC1210CCA | (2) TGK8C | TMC1210CCA1K | 805 | |
| | 10 | 3 | — | 1 | 1 | TMC1610CCA | (2) TGK8C | TMC1610CCA1K | 820 | |
| | 10 | 3 | — | 1 | 1 | TMC2410CCA | (2) TGK12 | TMC2410CCA1K | 855 | |
| | 10 | 3 | — | 1 | 1 | TMC3210CCA | (2) TGK32 | TMC3210CCA1K | 870 | |
| | 10 | 3 | — | 1 | 1 | TMC2412CCA | (2) TGK24 | TMC2412CCA1K | 1025 | |
| | 10 | 3 | — | 1 | 1 | TMC3215CCA | (2) TGK24 | TMC3215CCA1K | 1215 | |
| | 14 | 2 | 3 | 2 | 1 | TMC4015CCA | (2) TGK32 | TMC4015CCA3K | 1540 | |
| | 10 | 3 | — | 1 | 1 | TMC2020CCA | (2) TGK12 | TMC2020CCA1K | 1165 | |
| | 10 | 3 | — | 1 | 1 | TMC3220CCA | (2) TGK12 | TMC3220CCA1K | 1215 | |
| | 10 | 3 | — | 1 | 1 | TMC4020CCA | (2) TGK24 | TMC4020CCA1K | 1290 | |
| 14 | 2 | 3 | 2 | 1 | TMC4020CCA | (2) TGK42 | TMC4020CCA3K | 1540 | | |

Commercial Load Centers

Factory Installed Main Lugs & Equipment Ground Kit – Indoor Type 1 Enclosure
 Three Phase, Four-Wire, 208Y/120Vac

| Amps | Maximum Spaces (1" THQL) | | | Total 1-pole Spaces | Indoor Type 1 Enclosure | | Outdoor Type 3R Enclosure | | Equipment Ground Kit Installed |
|------|--------------------------|----|----|---------------------|---------------------------|---------------------|---------------------------|---------------------|--------------------------------|
| | 1P | 2P | 3P | | Catalog Number | List Price, GO-137E | Catalog Number | List Price, GO-137E | |
| 125 | 12 | 6 | 4 | 12 | TLC12412C | \$269 | TLC12412R | \$340 | TGK12 |
| 150 | 18 | 8 | 6 | 18 | TLC18415C | 315 | — | — | TGK12 |
| 150 | 24 | 12 | 8 | 24 | TLC24415C | 328 | TLC24415R | 435 | TGK24 |
| 200 | 18 | 8 | 6 | 18 | TLC18420C | 349 | — | — | TGK12 |
| 200 | 30 | 14 | 10 | 30 | TLC30420C | 395 | TLC30420R | 520 | TGK32 |
| 200 | 42 | 20 | 14 | 42 | TLC42420C | 448 | TLC42420R | 696 | TGK42 |
| 225 | 30 | 14 | 10 | 30 | TLC30422C | 412 | — | — | (2) TGL2 |
| 225 | 42 | 20 | 14 | 42 | TLC42422C | 661 | — | — | (2) TGL2 |
| 400 | 42 | 20 | 14 | 42 | TLC42440S, F ^① | 1797 | — | — | (2) TGL2 |
| 600 | 42 | 20 | 14 | 42 | TLC42460S, F ^① | 2010 | — | — | (2) TGL2 |

① Suffix S indicates surface mount enclosure; F indicates flush mount enclosure.

Service Entrance

Factory Installed Main Breaker & Equipment Ground Kit
 Three Phase, Four-Wire, 208Y/120Vac

| Amps | Maximum Spaces (1" THQL) | | | Total 1-pole Spaces | Indoor Type 1 Enclosure | | Outdoor Type 3R Enclosure | | Equipment Ground Kit Installed |
|------|--------------------------|----|----|---------------------|-------------------------|---------------------|---------------------------|---------------------|--------------------------------|
| | 1P | 2P | 3P | | Catalog Number | List Price, GO-137E | Catalog Number | List Price, GO-137E | |
| 100 | 12 | 6 | 4 | 12 | TMC12410C | \$374 | — | — | TGK12 |
| 100 | 18 | 8 | 6 | 18 | TMC18410C | 567 | TMC18410R | \$676 | TGK12 |
| 125 | 30 | 14 | 10 | 30 | TMC30412C | 957 | — | — | TGK24 |
| 200 | 42 | 20 | 14 | 42 | TMC42420C | 1072 | TMC42420R | 435 | TGK12 |

① Suffix S indicates surface mount enclosure; F indicates flush mount enclosure.