

Load Centers

Factory Installed Main Lugs & Equipment Ground Kit Single Phase, Three-Wire, 120/240Vac

Amps	Maximum Spaces				Total 1-pole Spaces	Indoor Type 1 Enclosure		Outdoor Type 3R Enclosure		Equipment Ground Kit Installed
	1" THQL		1/2" THQP			Catalog Number	List Price, GO-137E	Catalog Number	List Price, GO-137E	
	1P	2P	1P	2P						
40	2	1	4	1	4	TLC240SCU	\$67	TLC240RCU	\$86	TGK4
70	2	1	4	1	4	TLC270SCU	77	TLC270RCU	96	TGK4
100	4	2	8	3	8	TLC410C	95	TLC410R1	109	TGL1
	4	2	8	3	8	TPLC410C ^①	105	TPLC410R ^①	119	TGL1
125	6	3	12	4	12	TLC612SCU, FCU ^②	115	—	—	TGK12
	6	3	12	4	12	TLC612SCUD, FCUD ^{②③}	124	—	—	TGK12
	8	4	16	6	16	TLC812SCU, FCU ^②	126	TLC812RCU	159	TGK12
	8	4	16	6	16	TLC812SCUD, FCUD ^{②③}	135	—	—	TGK12
	12	6	24	10	24	TLC1212CCA	215	TLC1212RCA	290	(2) TGK8C ^⑤
	16	8	32	14	32	TLC1612CCA	230	—	—	(2) TGK8C
	24	12	48	22	48	TLC2412CCA	290	TLC2412RCA	395	(2) TGK12
200	16	8	32	14	32	TLC1620CCA	360	—	—	(2) TGK12
	20	10	40	18	40	TLC2020CCA	375	—	—	(2) TGK12
	32	16	64	30	64	TLC3220CCA	425	—	—	(2) TGK24
	40	20	80	38	80	TLC4020CCA	480	TLC4020RCA	690	(2) TGK24
225	42	20	84	40	84	TLC4222CCA	640	—	—	(2) TGK32
400	42	20	84	40	84	TLC4240S, F ^④	1523	—	—	(3) TGL2

① Thermoplastic enclosure.

② SCU indicates surface mount enclosure; FCU indicates flush mount enclosure.

③ Includes optional door.

④ Suffix S indicates surface mount enclosure; F indicates flush mount enclosure.

⑤ (2) TGK12 equipment ground kit installed on outdoor Type 3R enclosure.

Factory Installed Main Breaker & Equipment Ground Kit Single Phase, Three-Wire, 120/240Vac

Amps	Maximum Spaces				Total 1-pole Spaces	Indoor Type 1 Enclosure		Outdoor Type 3R Enclosure		Equipment Ground Kit Installed
	1" THQL		1/2" THQP			Catalog Number	List Price, GO-137E	Catalog Number	List Price, GO-137E	
	1P	2P	1P	2P						
100	12	6	24	10	24	TMC1210CCA	\$290	TMC1210RCA	\$565	(2) TGK8C ^①
100	16	8	32	14	32	TMC1610CCA	305	—	—	(2) TGK8C
100	20	10	40	18	40	TMC2010CCA	320	—	—	(2) TGK12
100	24	12	48	22	48	TMC2410CCA	340	—	—	(2) TGK12
100	32	16	64	30	64	TMC3210CCA	350	—	—	(2) TGK24
125	16	8	32	14	32	TMC1612CCA	450	—	—	(2) TGK8C
125	20	10	40	18	40	TMC2012CCA	470	—	—	(2) TGK12
125	24	12	48	22	48	TMC2412CCA	485	—	—	(2) TGK12
125	32	16	64	30	64	TMC3212CCA	505	—	—	(2) TGK24
150	20	10	40	18	40	TMC2015CCA	610	—	—	(2) TGK12
150	24	12	48	22	48	TMC2415CCA	640	—	—	(2) TGK12
150	32	16	64	30	64	TMC3215CCA	655	—	—	(2) TGK24
150	40	20	80	38	80	TMC4015CCA	725	—	—	(2) TGK32
200	20	10	40	18	40	TMC2020CCA	610	TMC2020RCA	670	(2) TGK12
200	32	16	64	30	64	TMC3220CCA	655	—	—	(2) TGK24
200	40	20	80	38	80	TMC4020CCA	725	—	—	(2) TGK24

① (2) TGK12 equipment ground kit installed on outdoor Type 3R enclosure.