

# Dry Type Transformers General Purpose Encapsulated Single-Phase NEMA 3R

## Section 10

.050 - 3 kVA Indoor/Outdoor Type QB UL Listed C-UL Listed

Input Voltage	Output Voltage	kVA	Frequency (Hz)	Taps	Wiring Diagram No. <sup>1</sup>	Weight (Lbs)	Frame Size	Product Number
240 x 480 Volts, 480 Volts	120/240 Volts	0.05	60 Hz	No Taps	1	6	6100	9T51B0002
240 x 480 Volts	120/240 Volts	0.05	50 Hz	No Taps	1	6	6100	9T51B0502
240 x 480 Volts, 480 Volts	120/240 Volts	0.075	60 Hz	No Taps	1	6	6200	9T51B0003
240 x 480 Volts	120/240 Volts	0.075	50 Hz	No Taps	1	6	6200	9T51B0503
240 x 480 Volts, 480 Volts	120/240 Volts	0.1	60 Hz	No Taps	1	6	6200	9T51B0004
240 x 480 Volts	120/240 Volts	0.1	50 Hz	No Taps	1	6	6200	9T51B0504
240 x 480 Volts, 480 Volts	120/240 Volts	0.15	60 Hz	No Taps	1	10	8175	9T51B0005
240 x 480 Volts	120/240 Volts	0.15	50 Hz	No Taps	1	10	8175	9T51B0505
240 x 480 Volts, 480 Volts	120/240 Volts	0.25	60 Hz	No Taps	1	10	8175	9T51B0007
240 x 480 Volts	120/240 Volts	0.25	50 Hz	No Taps	1	10	8200	9T51B0507
240 x 480 Volts, 480 Volts	120/240 Volts	0.5	60 Hz	No Taps	1	16	10200	9T51B0008
240 x 480 Volts	120/240 Volts	0.5	50 Hz	No Taps	1	20	10225	9T51B0508
240 x 480 Volts, 480 Volts	120/240 Volts	0.75	60 Hz	No Taps	1	25	12200	9T51B0009
240 x 480 Volts	120/240 Volts	0.75	50 Hz	No Taps	1	25	12225	9T51B0509
240 x 480 Volts, 480 Volts	120/240 Volts	1	60 Hz	No Taps	1	25	12225	9T51B0010
240 x 480 Volts	120/240 Volts	1	50 Hz	No Taps	1	30	12275	9T51B0510
240 x 480 Volts, 480 Volts	120/240 Volts	1.5	60 Hz	No Taps	1	40	14200	9T51B0011
240 x 480 Volts	120/240 Volts	1.5	50 Hz	No Taps	1	40	14225	9T51B0511
240 x 480 Volts, 480 Volts	120/240 Volts	2	60 Hz	No Taps	1	45	14250	9T51B0012
240 x 480 Volts	120/240 Volts	2	50 Hz	No Taps	1	50	14300	9T51B0512
240 x 480 Volts, 480 Volts	120/240 Volts	3	60 Hz	No Taps	1	55	14350	9T51B0013
240 x 480 Volts	120/240 Volts	3	50 Hz	No Taps	1	60	14400	9T51B0513
480 Volts	120/240 Volts	0.5	50 Hz	(-2 5.0%)	2	20	10225	9T51B0548
480 Volts	120/240 Volts	0.75	50 Hz	(-2 5.0%)	2	25	12200	9T51B0549
480 Volts	120/240 Volts	1	60 Hz	(-2 5.0%)	2	25	12225	9T51B0050
480 Volts	120/240 Volts	1	50 Hz	(-2 5.0%)	2	30	12275	9T51B0550
480 Volts	120/240 Volts	1.5	60 Hz	(-2 5.0%)	2	40	14200	9T51B0051
480 Volts	120/240 Volts	1.5	50 Hz	(-2 5.0%)	2	40	14225	9T51B0551
480 Volts	120/240 Volts	2	60 Hz	(-2 5.0%)	2	45	14250	9T51B0052
480 Volts	120/240 Volts	2	50 Hz	(-2 5.0%)	2	50	14300	9T51B0552
480 Volts	120/240 Volts	3	60 Hz	(-2 5.0%)	2	55	14350	9T51B0053
480 Volts	120/240 Volts	3	60 Hz	(+2,-2 2.5%)	3	55	14350	9T51B0135
480 Volts	120/240 Volts	3	50 Hz	(-2 5.0%)	2	60	14400	9T51B0553
600 Volts	120/240 Volts	0.05	60 Hz	No Taps	5	6	6100	9T51B0082
600 Volts	120/240 Volts	0.075	60 Hz	No Taps	5	6	6200	9T51B0083
600 Volts	120/240 Volts	0.1	60 Hz	No Taps	5	6	6200	9T51B0084
600 Volts	120/240 Volts	0.1	50 Hz	No Taps	5	6	6200	9T51B0584
600 Volts	120/240 Volts	0.15	60 Hz	No Taps	5	10	8175	9T51B0085
600 Volts	120/240 Volts	0.25	60 Hz	No Taps	5	10	8175	9T51B0087
600 Volts	120/240 Volts	0.25	50 Hz	No Taps	5	10	8200	9T51B0587
600 Volts	120/240 Volts	0.5	60 Hz	No Taps	5	16	10200	9T51B0088
600 Volts	120/240 Volts	0.5	50 Hz	(-2 5.0%)	2	20	10225	9T51B0568
600 Volts	120/240 Volts	0.75	60 Hz	No Taps	5	25	12200	9T51B0089
600 Volts	120/240 Volts	0.75	50 Hz	(-2 5.0%)	2	25	12200	9T51B0569
600 Volts	120/240 Volts	1	60 Hz	(-2 5.0%)	2	25	12225	9T51B0070
600 Volts	120/240 Volts	1	60 Hz	No Taps	5	25	12225	9T51B0090
600 Volts	120/240 Volts	1	50 Hz	(-2 5.0%)	2	30	12275	9T51B0570
600 Volts	120/240 Volts	1.5	60 Hz	(-2 5.0%)	2	40	14200	9T51B0071
600 Volts	120/240 Volts	1.5	60 Hz	No Taps	5	40	14200	9T51B0091
600 Volts	120/240 Volts	1.5	50 Hz	(-2 5.0%)	2	40	14225	9T51B0571
600 Volts	120/240 Volts	2	60 Hz	(-2 5.0%)	2	45	14250	9T51B0072
600 Volts	120/240 Volts	2	60 Hz	No Taps	5	45	14250	9T51B0092
600 Volts	120/240 Volts	2	50 Hz	(-2 5.0%)	2	50	14300	9T51B0572
600 Volts	120/240 Volts	2	50 Hz	No Taps	5	50	14300	9T51B0592
600 Volts	120/240 Volts	3	60 Hz	(-2 5.0%)	2	55	14350	9T51B0073
600 Volts	120/240 Volts	3	60 Hz	No Taps	5	55	14350	9T51B0093
600 Volts	120/240 Volts	3	50 Hz	(-2 5.0%)	2	60	14400	9T51B0573
600 Volts	120/240 Volts	3	50 Hz	No Taps	5	60	14400	9T51B0593

<sup>1</sup>See page 10-45 for wiring diagrams.

