

**Energy Saver®**  
TEFC—Severe Duty

Pricing

Volts: 230/460, 460, 575  
HP: 1 - 250



HP	RPM	Volts	Frame	FLA	Nom. Eff.	Cat. No.	List Price	Price Symbol	Norm. Stk.	Wt. (lbs.)	C Dim. (in.)	C-Face Cat. #	Notes
1	3600	230/460	143T	2.8/1.4	77.0	M7700	\$492	G4-7S\$P1	Y	47	12.25	A1064	29, 105, 131
1	3600	575	143T	1.1	77.0	M7500	\$492	G4-7S\$P1	N	47	12.4	A1064	
1	1800	230/460	143T	2.8/1.4	85.5	M7723	\$498	G4-7S\$P1	Y	46	12.25	A1064	29, 105, 131
1	1800	575	143T	1.1	85.5	M7523	\$498	G4-7S\$P1	Y	46	12.4	A1064	
1	1200	230/460	145T	3.4/1.7	82.5	M7540	\$660	G4-7S\$P1	Y	51	13.4	A1064	29, 105, 131
1.5	3600	230/460	143T	3.8/1.9	84.0	M7701	\$534	G4-7S\$P1	Y	47	12.25	A1064	29, 105, 131
1.5	1800	230/460	145T	4.2/2.1	86.5	M7724	\$554	G4-7S\$P1	Y	60	13.24	A1064	29, 105, 131
1.5	1800	230/460	145T	4.2/2.1	86.5	M7624	\$554	G4-7S\$P1	Y	60	13.24	A1064	29, 70, 105, 131
1.5	1800	575	145T	1.7	86.5	M7524	\$554	G4-7S\$P1	Y	60	13.4	A1064	
1.5	1200	230/460	182T	4.8/2.4	87.5	M7541	\$750	G4-7S\$P1	Y	93	14.59	A1065	29, 105, 131
2	3600	230/460	145T	4.8/2.4	85.5	M7702	\$639	G4-7S\$P1	Y	63	13.24	A1064	29, 105, 131
2	3600	575	145T	1.9	85.5	M7502	\$639	G4-7S\$P1	N	63	13.4	A1064	
2	1800	230/460	145T	5.4/2.7	86.5	M7725	\$609	G4-7S\$P1	Y	60	13.24	A1064	29, 105, 131
2	1800	230/460	145T	5.4/2.7	86.5	M7625	\$609	G4-7S\$P1	Y	60	13.24	A1064	70
2	1800	575	145T	2.2	86.5	M7525	\$609	G4-7S\$P1	Y	60	13.4	A1064	
2	1200	230/460	184T	6.6/3.3	88.5	M7542	\$840	G4-7S\$P1	Y	106	15.57	A1065	29, 105, 131
3	3600	230/460	182T	7.2/3.6	86.5	M7703	\$719	G4-7S\$P1	Y	82	14.43	A1065	29, 105, 131
3	3600	575	182T	2.9	86.5	M7503	\$719	G4-7S\$P1	N	82	14.59	A1065	
3	1800	230/460	182T	7.6/3.8	89.5	M7726	\$675	G4-7S\$P1	Y	86	14.43	A1065	29, 105, 131
3	1800	230/460	182T	7.6/3.8	89.5	M7626	\$675	G4-7S\$P1	Y	86	14.43	A1065	29, 70, 105, 131
3	1800	575	182T	3.0	89.5	M7526	\$690	G4-7S\$P1	Y	86	14.59	A1065	
3	1200	230/460	213T	8.2/4.1	89.5	M7543	\$1,020	G4-7S\$P1	Y	139	17.78	A1066	29, 105, 131
5	3600	230/460	184T	11.4/5.7	88.5	M7704	\$890	G4-7S\$P1	Y	106	15.42	A1065	29, 105, 131
5	3600	575	184T	4.6	88.5	M7504	\$890	G4-7S\$P1	N	106	15.57	A1065	
5	1800	230/460	184T	12.6/6.3	89.5	M7727	\$788	G4-7S\$P1	Y	111	15.42	A1065	29, 105, 131
5	1800	230/460	184T	12.6/6.3	89.5	M7627	\$788	G4-7S\$P1	Y	111	15.42	A1065	29, 70, 105, 131
5	1800	575	184T	5.0	89.5	M7527	\$788	G4-7S\$P1	Y	111	15.57	A1065	
5	1200	230/460	215T	13.6/6.8	89.5	M7544	\$1,425	G4-7S\$P1	Y	168	19.27	A1066	29, 105, 131
7.5	3600	230/460	213T	18/9	89.5	M7705	\$1,076	G4-7S\$P1	Y	149	17.94	A1066	29, 105, 131
7.5	3600	230/460	213T	18/9	89.5	M7605	\$1,076	G4-7S\$P1	Y	149	17.94	A1066	29, 70, 105, 131
7.5	3600	575	213T	7.2	89.5	M7505	\$1,076	G4-7S\$P1	N	149	17.78	A1066	
7.5	1800	230/460	213T	18.2/9.1	91.7	M7728	\$1,070	G4-7S\$P1	Y	158	17.94	A1066	29, 105, 131
7.5	1800	230/460	213T	18.2/9.1	91.7	M7628	\$1,070	G4-7S\$P1	Y	158	17.94	A1066	29, 70, 105, 131
7.5	1800	575	213T	7.3	91.7	M7528	\$1,070	G4-7S\$P1	Y	158	17.78	A1066	
7.5	1200	230/460	254T	19.6/9.8	91.0	M7545	\$1,800	G4-7S\$P1	Y	234	23.70	A1067	29, 105, 131

Notes:

- 29 Usable on 200 Volts, 60Hz at 1.0 service factor
- 70 F2 Assembly
- 105 Usable on 200/400V, 50Hz, same HP, at 1.0 service factor
- 131 Usable on 200/400V, 50Hz at 1.15SF and de-rated to next lower HP