

X\$D Ultra® 841
TEFC—Extra Severe Duty

Pricing



Volts: 460, 575
HP: 0.75 – 250

HP	RPM	Volts	Frame	FLA	Nom. Eff.	Guar. Min. Eff.	Cat. No.	List Price	Price Symbol	Norm. Stk.	Wt. (lbs)	C Dim. (in)	Notes
0.75	1200	460	143T	1.4	80.0	78.5	M354	\$1,008	G4-7UX1	N	43	13.40	
0.75	1200	575	143T	1.1	80.0	78.5	M355	\$1,008	G4-7UX1	N	43	13.40	
0.75	900	460	145T	1.9	72.0	70.0	M8901	\$1,662	G4-7UX1	N	50	13.40	
1	3600	460	143T	1.3	87.5	86.5	M8903	\$1,035	G4-7UX1	N	43	11.60	55
1	3600	575	143T	1.1	87.5	86.5	M8904	\$1,035	G4-7UX1	N	43	11.60	55
1	1800	460	143T	1.4	86.5	85.5	M352	\$1,020	G4-7UX1	Y	43	11.60	
1	1800	575	143T	1.2	86.5	85.5	M353	\$1,020	G4-7UX1	Y	43	11.60	
1	1200	460	145T	1.8	82.5	81.5	M363	\$1,092	G4-7UX1	Y	50	13.40	
1	1200	575	145T	1.5	82.5	81.5	M364	\$1,092	G4-7UX1	N	50	13.40	
1	900	460	182T	2.2	80.0	78.5	M9413	\$1,334	G4-7UX1	N	76	15.90	55
1	900	575	182T	1.8	80.0	78.5	M9482	\$1,334	G4-7UX1	N	76	15.90	55
1.5	3600	460	143T	2.0	87.5	86.5	M8905	\$1,080	G4-7UX1	Y	43	11.60	55
1.5	3600	575	143T	1.6	87.5	86.5	M8906	\$1,080	G4-7UX1	N	43	11.60	55
1.5	1800	460	145T	2.1	86.5	85.5	M359	\$1,157	G4-7UX1	Y	50	11.60	
1.5	1800	575	145T	1.7	86.5	85.5	M360	\$1,157	G4-7UX1	Y	50	11.60	
1.5	1200	460	182T	2.4	87.5	86.5	M9414	\$1,194	G4-7UX1	Y	76	15.90	
1.5	1200	575	182T	1.9	87.5	86.5	M9483	\$1,194	G4-7UX1	N	76	15.90	
1.5	900	460	184T	3.2	80.0	78.5	M9415	\$1,577	G4-7UX1	N	101	15.90	
1.5	900	575	184T	2.6	80.0	78.5	M9485	\$1,577	G4-7UX1	N	101	15.90	
2	3600	460	145T	2.7	86.5	85.5	M8907	\$1,293	G4-7UX1	Y	43	11.60	55
2	3600	575	145T	2.2	86.5	85.5	M8908	\$1,293	G4-7UX1	N	43	11.60	55
2	1800	460	145T	2.7	86.5	85.5	M361	\$1,250	G4-7UX1	Y	50	13.40	
2	1800	575	145T	2.2	86.5	85.5	M362	\$1,250	G4-7UX1	Y	50	13.40	
2	1200	460	184T	3.0	88.5	87.5	M9416	\$1,278	G4-7UX1	Y	101	15.90	
2	1200	575	184T	2.5	88.5	87.5	M9486	\$1,278	G4-7UX1	Y	101	15.90	
2	900	460	213T	3.8	86.5	85.5	M9417	\$2,031	G4-7UX1	N	200	20.10	
2	900	575	213T	3.0	86.5	85.5	M9487	\$2,031	G4-7UX1	N	200	20.10	
3	3600	460	182T	3.9	89.5	88.5	M9418	\$1,178	G4-7UX1	Y	76	15.90	55
3	3600	575	182T	3.1	89.5	88.5	M9488	\$1,178	G4-7UX1	N	76	15.90	55
3	1800	460	182T	4.2	89.5	88.5	M9419	\$1,112	G4-7UX1	Y	76	15.90	55
3	1800	575	182T	3.3	89.5	88.5	M9489	\$1,112	G4-7UX1	Y	76	15.90	55
3	1200	460	213T	4.2	89.5	88.5	M9420	\$1,425	G4-7UX1	Y	200	20.10	
3	1200	575	213T	3.4	89.5	88.5	M9490	\$1,425	G4-7UX1	Y	200	20.10	
3	900	460	215T	5.4	86.5	85.5	M9421	\$2,621	G4-7UX1	N	220	20.10	
3	900	575	215T	4.3	86.5	85.5	M9491	\$2,621	G4-7UX1	N	220	20.10	

Notes:
55 TENV Construction

2.19
X\$D Ultra® 841