

X\$D Ultra® 841
TEFC—Extra Severe Duty

Pricing (cont.)



Volts: 460, 575
HP: 0.75 – 250

HP	RPM	Volts	Frame	FLA	Nom. Eff.	Guar. Min. Eff.	Cat. No.	List Price	Price Symbol	Norm. Stk.	Wt. (lbs)	C Dim. (in)	Notes
5	3600	460	184T	6.3	90.2	89.5	M9422	\$1,334	G4-7UX1	Y	101	15.90	
5	3600	575	184T	5.0	90.2	89.5	M9492	\$1,334	G4-7UX1	N	101	15.90	
5	1800	460	184T	6.6	89.5	88.5	M9423	\$1,182	G4-7UX1	Y	101	15.90	
5	1800	575	184T	5.3	89.5	88.5	M9493	\$1,182	G4-7UX1	Y	101	15.90	
5	1200	460	215T	7.2	89.5	88.5	M9424	\$2,007	G4-7UX1	Y	220	20.10	
5	1200	575	215T	5.4	89.5	88.5	M9494	\$2,007	G4-7UX1	Y	220	20.10	
5	900	460	254T	8.1	89.5	88.5	M9425	\$3,615	G4-7UX1	N	315	25.60	
5	900	575	254T	6.5	89.5	88.5	M9495	\$3,615	G4-7UX1	N	315	25.60	
7.5	3600	460	213T	8.5	91.0	90.2	M9426	\$1,740	G4-7UX1	Y	200	20.10	
7.5	3600	575	213T	6.8	91.0	90.2	M9496	\$1,740	G4-7UX1	N	200	20.10	
7.5	1800	460	213T	9.1	91.7	91.0	M9427	\$1,730	G4-7UX1	Y	200	20.10	
7.5	1800	575	213T	7.2	91.7	91.0	M9497	\$1,730	G4-7UX1	Y	200	20.10	
7.5	1200	460	254T	9.8	91.7	91.0	M9428	\$2,667	G4-7UX1	Y	315	25.60	
7.5	1200	575	254T	7.9	91.7	91.0	M9498	\$2,667	G4-7UX1	Y	315	25.60	
7.5	900	460	256T	11.6	89.5	88.5	M9429	\$4,577	G4-7UX1	N	350	25.60	
7.5	900	575	256T	9.3	89.5	88.5	M9499	\$4,577	G4-7UX1	N	350	25.60	
10	3600	460	215T	11.2	91.0	90.2	M9430	\$1,883	G4-7UX1	Y	220	20.10	
10	3600	575	215T	9.0	91.0	90.2	M9563	\$1,883	G4-7UX1	N	220	20.10	
10	1800	460	215T	12.0	91.7	91.0	M9431	\$1,929	G4-7UX1	Y	220	20.10	
10	1800	575	215T	9.6	91.7	91.0	M9564	\$1,929	G4-7UX1	Y	220	20.10	
10	1200	460	256T	13.1	91.0	90.2	M9432	\$3,260	G4-7UX1	Y	350	25.60	
10	1200	575	256T	10.5	91.0	90.2	M9565	\$3,260	G4-7UX1	Y	350	25.60	
10	900	460	284T	13.8	90.2	89.5	M9433	\$5,426	G4-7UX1	N	460	28.58	
10	900	575	284T	11.0	90.2	89.5	M9566	\$5,426	G4-7UX1	N	460	28.58	
15	3600	460	254T	17.6	91.7	91.0	M9434	\$2,588	G4-7UX1	Y	315	25.60	
15	3600	575	254T	14.0	91.7	91.0	M9567	\$2,588	G4-7UX1	N	315	25.60	
15	1800	460	254T	18.0	92.4	91.7	M9435	\$2,541	G4-7UX1	Y	315	25.60	
15	1800	575	254T	14.4	92.4	91.7	M9568	\$2,541	G4-7UX1	Y	315	25.60	
15	1200	460	284T	19.6	91.7	91.0	M9436	\$4,323	G4-7UX1	Y	460	28.58	
15	1200	575	284T	15.7	91.7	91.0	M9569	\$4,323	G4-7UX1	Y	460	28.58	
15	900	460	286T	20.5	90.2	89.5	M9437	\$7,089	G4-7UX1	N	510	28.58	
15	900	575	286T	16.4	90.2	89.5	M9570	\$7,089	G4-7UX1	N	510	28.58	
20	3600	460	256T	22.6	92.4	91.7	M9438	\$3,203	G4-7UX1	Y	350	25.60	
20	3600	575	256T	18.1	92.4	91.7	M9571	\$3,203	G4-7UX1	N	350	25.60	
20	1800	460	256T	23.3	93.0	92.4	M9439	\$3,167	G4-7UX1	Y	350	25.60	
20	1800	575	256T	18.6	93.0	92.4	M9572	\$3,167	G4-7UX1	Y	350	25.60	

2.20

X\$D Ultra® 841