

**X\$D Ultra® 841**  
TEFC—Extra Severe Duty

Pricing (cont.)

Volts: 460, 575  
HP: 0.75 – 250



| HP | RPM  | Volts | Frame | FLA  | Nom. Eff. | Guar. Min. Eff. | Cat. No. | List Price | Price Symbol | Norm. Stk. | Wt. (lbs) | C Dim. (in) | Notes |
|----|------|-------|-------|------|-----------|-----------------|----------|------------|--------------|------------|-----------|-------------|-------|
| 20 | 1200 | 460   | 286T  | 26.0 | 91.7      | 91.0            | M9440    | \$5,268    | G4-7UX1      | Y          | 510       | 28.58       |       |
| 20 | 1200 | 575   | 286T  | 20.8 | 91.7      | 91.0            | M9573    | \$5,268    | G4-7UX1      | Y          | 510       | 28.58       |       |
| 20 | 900  | 460   | 324T  | 29.8 | 91.0      | 90.2            | M9441    | \$8,189    | G4-7UX1      | N          | 649       | 30.54       |       |
| 20 | 900  | 575   | 324T  | 23.9 | 91.0      | 90.2            | M9574    | \$8,189    | G4-7UX1      | N          | 649       | 30.54       |       |
| 25 | 3600 | 460   | 284TS | 27.8 | 93.0      | 92.4            | M9442    | \$3,948    | G4-7UX1      | Y          | 460       | 27.20       |       |
| 25 | 3600 | 575   | 284TS | 22.2 | 93.0      | 92.4            | M9575    | \$3,948    | G4-7UX1      | N          | 460       | 27.20       |       |
| 25 | 1800 | 460   | 284T  | 29.8 | 93.6      | 93.0            | M9443    | \$3,771    | G4-7UX1      | Y          | 460       | 28.58       |       |
| 25 | 1800 | 575   | 284T  | 23.8 | 93.6      | 93.0            | M9576    | \$3,771    | G4-7UX1      | Y          | 460       | 28.58       |       |
| 25 | 1200 | 460   | 324T  | 32.3 | 93.0      | 92.4            | M9444    | \$6,669    | G4-7UX1      | Y          | 679       | 30.54       |       |
| 25 | 1200 | 575   | 324T  | 25.8 | 93.0      | 92.4            | M9577    | \$6,669    | G4-7UX1      | Y          | 679       | 30.54       |       |
| 25 | 900  | 460   | 326T  | 37.0 | 91.0      | 90.2            | M9445    | \$9,807    | G4-7UX1      | N          | 710       | 32.04       |       |
| 25 | 900  | 575   | 326T  | 29.2 | 91.0      | 90.2            | M9578    | \$9,807    | G4-7UX1      | N          | 710       | 32.04       |       |
| 30 | 3600 | 460   | 286TS | 33.4 | 93.0      | 92.4            | M9446    | \$4,610    | G4-7UX1      | Y          | 510       | 27.20       |       |
| 30 | 3600 | 575   | 286TS | 26.7 | 93.0      | 92.4            | M9579    | \$4,610    | G4-7UX1      | N          | 510       | 27.20       |       |
| 30 | 1800 | 460   | 286T  | 35.5 | 93.6      | 93.0            | M9447    | \$4,383    | G4-7UX1      | Y          | 510       | 28.58       |       |
| 30 | 1800 | 575   | 286T  | 28.4 | 93.6      | 93.0            | M9580    | \$4,383    | G4-7UX1      | Y          | 510       | 28.58       |       |
| 30 | 1200 | 460   | 326T  | 38.2 | 93.0      | 92.4            | M9448    | \$7,443    | G4-7UX1      | Y          | 730       | 32.04       |       |
| 30 | 1200 | 575   | 326T  | 30.8 | 93.0      | 92.4            | M9581    | \$7,443    | G4-7UX1      | Y          | 730       | 32.04       |       |
| 30 | 900  | 460   | 364T  | 42.2 | 92.4      | 91.7            | M9449    | \$12,110   | G4-7UX       | N          | 1010      | 34.89       |       |
| 30 | 900  | 575   | 364T  | 33.8 | 92.4      | 91.7            | M9582    | \$12,110   | G4-7UX       | N          | 1010      | 34.89       |       |
| 40 | 3600 | 460   | 324TS | 46.8 | 94.1      | 93.6            | M9450    | \$6,264    | G4-7UX1      | Y          | 649       | 29.04       |       |
| 40 | 3600 | 575   | 324TS | 37.4 | 94.1      | 93.6            | M9583    | \$6,264    | G4-7UX1      | N          | 649       | 29.04       |       |
| 40 | 1800 | 460   | 324T  | 50.8 | 94.5      | 94.1            | M9451    | \$6,077    | G4-7UX1      | Y          | 689       | 30.54       |       |
| 40 | 1800 | 575   | 324T  | 40.6 | 94.5      | 94.1            | M9584    | \$6,077    | G4-7UX1      | Y          | 689       | 30.54       |       |
| 40 | 1200 | 460   | 364T  | 49.4 | 94.1      | 93.6            | M9452    | \$9,950    | G4-7UX       | Y          | 1030      | 34.89       |       |
| 40 | 1200 | 575   | 364T  | 39.8 | 94.1      | 93.6            | M9585    | \$9,950    | G4-7UX       | Y          | 1030      | 34.89       |       |
| 40 | 900  | 460   | 365T  | 55.9 | 93.0      | 92.4            | M9453    | \$14,937   | G4-7UX       | N          | 1090      | 34.89       |       |
| 40 | 900  | 575   | 365T  | 45.0 | 93.0      | 92.4            | M9586    | \$14,937   | G4-7UX       | N          | 1090      | 34.89       |       |
| 50 | 3600 | 460   | 326TS | 57.3 | 94.5      | 94.1            | M9454    | \$7,647    | G4-7UX1      | Y          | 700       | 30.48       |       |
| 50 | 3600 | 575   | 326TS | 45.5 | 94.5      | 94.1            | M9587    | \$7,647    | G4-7UX1      | N          | 700       | 30.48       |       |
| 50 | 1800 | 460   | 326T  | 63.9 | 94.5      | 94.1            | M9455    | \$6,923    | G4-7UX1      | Y          | 740       | 32.04       |       |
| 50 | 1800 | 575   | 326T  | 51.1 | 94.5      | 94.1            | M9588    | \$6,923    | G4-7UX1      | Y          | 740       | 32.04       |       |
| 50 | 1200 | 460   | 365T  | 62.2 | 94.1      | 93.6            | M9456    | \$11,343   | G4-7UX       | Y          | 1070      | 34.89       |       |
| 50 | 1200 | 575   | 365T  | 49.7 | 94.1      | 93.6            | M9589    | \$11,343   | G4-7UX       | Y          | 1070      | 34.89       |       |
| 50 | 900  | 460   | 404T  | 66.6 | 93.0      | 92.4            | M9457    | \$18,023   | G4-7UX       | N          | 1490      | 39.77       |       |
| 50 | 900  | 575   | 404T  | 53.0 | 93.0      | 92.4            | M9590    | \$18,023   | G4-7UX       | N          | 1490      | 39.77       |       |