

X\$D Ultra® 841
TEFC—Extra Severe Duty

Pricing (cont.)



Volts: 460, 575
HP: 0.75 – 250

| HP | RPM | Volts | Frame | FLA | Nom. Eff. | Guar. Min. Eff. | Cat. No. | List Price | Price Symbol | Norm. Stk. | Wt. (lbs) | C Dim. (in) | Notes |
|-----|------|-------|-------|-------|-----------|-----------------|----------|------------|--------------|------------|-----------|-------------|-------|
| 60 | 3600 | 460 | 364TS | 70.4 | 95.0 | 94.5 | M9458 | \$10,256 | G4-7UX | Y | 940 | 32.76 | |
| 60 | 3600 | 575 | 364TS | 56.3 | 95.0 | 94.5 | M9591 | \$10,256 | G4-7UX | N | 940 | 32.76 | |
| 60 | 1800 | 460 | 364T | 71.2 | 95.0 | 94.5 | M9459 | \$9,924 | G4-7UX | Y | 1020 | 34.89 | |
| 60 | 1800 | 575 | 364T | 56.6 | 95.0 | 94.5 | M9592 | \$9,924 | G4-7UX | Y | 1020 | 34.89 | |
| 60 | 1200 | 460 | 404T | 72.5 | 95.0 | 94.5 | M9460 | \$13,245 | G4-7UX | Y | 1480 | 39.77 | |
| 60 | 1200 | 575 | 404T | 58.0 | 95.0 | 94.5 | M9593 | \$13,245 | G4-7UX | N | 1480 | 39.77 | |
| 60 | 900 | 460 | 405T | 78.9 | 93.0 | 92.4 | M9461 | \$20,340 | G4-7UX | N | 1570 | 39.77 | |
| 60 | 900 | 575 | 405T | 63.1 | 93.0 | 92.4 | M9594 | \$20,340 | G4-7UX | N | 1570 | 39.77 | |
| 75 | 3600 | 460 | 365TS | 85.2 | 95.8 | 95.4 | M9462 | \$12,261 | G4-7UX | Y | 1020 | 32.76 | |
| 75 | 3600 | 575 | 365TS | 68.6 | 95.8 | 95.4 | M8917 | \$12,261 | G4-7UX | N | 1020 | 32.76 | |
| 75 | 1800 | 460 | 365T | 86.6 | 95.4 | 95.0 | M9463 | \$11,759 | G4-7UX | Y | 1090 | 34.89 | |
| 75 | 1800 | 575 | 365T | 68.9 | 95.4 | 95.0 | M9596 | \$11,759 | G4-7UX | Y | 1090 | 34.89 | |
| 75 | 1200 | 460 | 405T | 89.6 | 95.0 | 94.5 | M9464 | \$14,547 | G4-7UX | Y | 1540 | 39.77 | |
| 75 | 1200 | 575 | 405T | 71.2 | 95.0 | 94.5 | M9597 | \$14,547 | G4-7UX | N | 1540 | 39.77 | |
| 75 | 900 | 460 | 444T | 94.0 | 94.5 | 94.1 | M9465 | \$25,449 | G4-7UX | N | 1950 | 45.62 | |
| 75 | 900 | 575 | 444T | 75.2 | 94.5 | 94.1 | M9598 | \$25,449 | G4-7UX | N | 1950 | 45.62 | |
| 100 | 3600 | 460 | 405TS | 108.0 | 95.4 | 95.0 | M9466 | \$15,783 | G4-7UX | Y | 1530 | 36.76 | |
| 100 | 3600 | 575 | 405TS | 86.3 | 95.4 | 95.0 | M8918 | \$15,783 | G4-7UX | N | 1530 | 36.76 | |
| 100 | 1800 | 460 | 405T | 119.0 | 95.8 | 95.4 | M9467 | \$14,477 | G4-7UX | Y | 1480 | 39.77 | |
| 100 | 1800 | 575 | 405T | 95.3 | 95.8 | 95.4 | M9693 | \$14,477 | G4-7UX | Y | 1480 | 39.77 | 113 |
| 100 | 1200 | 460 | 444T | 116.0 | 95.4 | 95.0 | M9468 | \$18,723 | G4-7UX | Y | 2060 | 45.62 | |
| 100 | 1200 | 575 | 444T | 93.0 | 95.4 | 95.0 | M9694 | \$18,723 | G4-7UX | N | 2060 | 45.62 | |
| 100 | 900 | 460 | 445T | 125.0 | 94.5 | 94.1 | M9469 | \$32,247 | G4-7UX | N | 2020 | 45.62 | |
| 100 | 900 | 575 | 445T | 100.0 | 94.5 | 94.1 | M9695 | \$32,247 | G4-7UX | N | 2020 | 45.62 | |
| 125 | 3600 | 460 | 444TS | 139.0 | 95.4 | 95.0 | M9470 | \$20,169 | G4-7UX | Y | 1790 | 41.87 | |
| 125 | 3600 | 575 | 444TS | 112.0 | 95.4 | 95.0 | M8919 | \$20,169 | G4-7UX | N | 1790 | 41.87 | |
| 125 | 1800 | 460 | 444T | 144.0 | 95.8 | 95.4 | M9471 | \$18,651 | G4-7UX | Y | 1970 | 45.62 | |
| 125 | 1800 | 575 | 444T | 115.0 | 95.8 | 95.4 | M9697 | \$18,651 | G4-7UX | Y | 1970 | 45.62 | |
| 125 | 1200 | 460 | 445T | 150.0 | 95.4 | 95.0 | M9472 | \$22,307 | G4-7UX | Y | 2130 | 45.62 | |
| 125 | 1200 | 575 | 445T | 120.0 | 95.4 | 95.0 | M9698 | \$22,307 | G4-7UX | N | 2130 | 45.62 | |
| 125 | 900 | 460 | 447T | 155.0 | 95.0 | 94.5 | M9473 | \$35,909 | G4-7UX | N | 2580 | 52.12 | |
| 125 | 900 | 575 | 447T | 124.0 | 95.0 | 94.5 | M9699 | \$35,909 | G4-7UX | N | 2580 | 52.12 | |
| 150 | 3600 | 460 | 445TS | 163.0 | 95.8 | 95.4 | M9474 | \$23,874 | G4-7UX | Y | 1930 | 41.87 | |
| 150 | 3600 | 575 | 445TS | 130.0 | 95.8 | 95.4 | M8920 | \$23,874 | G4-7UX | N | 1930 | 41.87 | |
| 150 | 1800 | 460 | 445T | 170.0 | 96.2 | 95.8 | M9475 | \$21,431 | G4-7UX | Y | 2090 | 45.62 | |
| 150 | 1800 | 575 | 445T | 137.0 | 96.2 | 95.8 | M9384 | \$21,431 | G4-7UX | Y | 2060 | 45.62 | |

Notes:

113 Bearing temperature exceeds IEEE-841