

X\$D Ultra®
TEFC—Extra Severe Duty (IP55)

Pricing (cont.)



Volts: 230/460, 460, 575
HP: 0.75 – 300

HP	RPM	Volts	Frame	FLA	Nom. Eff.	Guar. Min. Eff.	Cat. No.	List Price	Price Symbol	Norm. Stk.	Wt. (lbs)	C Dim. (in)	C-Face Kit	Notes
3	1800	230/460	182T	8.4/4.2	89.5	88.5	M241	\$975	G4-7U1	N	76	15.90	PB18A	55
3	1800	460	182T	4.2	89.5	88.5	M9941	\$975	G4-7U1	Y	76	15.90	PB18A	55
3	1800	575	182T	3.3	89.5	88.5	M9711	\$975	G4-7U1	Y	76	15.90	PB18A	55
3	1200	230/460	213T	8.4/4.2	89.5	88.5	M9142	\$1,230	G4-7U1	N	200	20.10	PB21A	
3	1200	460	213T	4.2	89.5	88.5	M9111	\$1,230	G4-7U1	Y	200	20.10	PB21A	
3	1200	575	213T	3.4	89.5	88.5	M9712	\$1,230	G4-7U1	N	200	20.10	PB21A	
3	900	230/460	215T	10.6/5.3	86.5	85.5	M9877	\$2,165	G4-7U1	Y	220	20.10	PB21A	
3	900	460	215T	5.3	86.5	85.5	M9708	\$2,165	G4-7U1	N	220	20.10	PB21A	
3	900	575	215T	4.3	86.5	85.5	M9878	\$2,165	G4-7U1	N	220	20.10	PB21A	
5	3600	230/460	184T	12.4/6.2	90.2	89.5	M240	\$1,068	G4-7U1	N	101	15.90	PB18A	
5	3600	460	184T	6.2	90.2	89.5	M9940	\$1,068	G4-7U1	Y	101	15.90	PB18A	
5	3600	575	184T	4.9	90.2	89.5	M9722	\$1,068	G4-7U1	Y	101	15.90	PB18A	
5	1800	230/460	184T	13.2/6.6	89.5	88.5	M242	\$1,026	G4-7U1	N	101	15.90	PB18A	
5	1800	460	184T	6.6	89.5	88.5	M9942	\$1,026	G4-7U1	Y	101	15.90	PB18A	
5	1800	575	184T	5.3	89.5	88.5	M9718	\$1,026	G4-7U1	Y	101	15.90	PB18A	
5	1200	230/460	215T	13.4/6.7	89.5	88.5	M9143	\$1,748	G4-7U1	N	220	20.10	PB21A	
5	1200	460	215T	6.7	89.5	88.5	M9112	\$1,748	G4-7U1	Y	220	20.10	PB21A	
5	1200	575	215T	5.4	89.5	88.5	M9717	\$1,748	G4-7U1	N	220	20.10	PB21A	
5	900	230/460	254T	16.0/8.0	89.5	88.5	M9879	\$2,876	G4-7U1	Y	315	25.60	PB25A	
5	900	460	254T	8.0	89.5	88.5	M9719	\$2,876	G4-7U1	N	315	25.60	PB25A	
5	900	575	254T	6.4	89.5	88.5	M9880	\$2,876	G4-7U1	N	315	25.60	PB25A	
7.5	3600	230/460	213T	17.0/8.5	91.0	90.2	M9144	\$1,524	G4-7U1	N	200	20.10	PB21A	
7.5	3600	460	213T	8.5	91.0	90.2	M990	\$1,524	G4-7U1	Y	200	20.10	PB21A	
7.5	3600	575	213T	6.8	91.0	90.2	M9728	\$1,524	G4-7U1	Y	200	20.10	PB21A	
7.5	1800	230/460	213T	18.2/9.1	91.7	91.0	M9145	\$1,515	G4-7U1	N	200	20.10	PB21A	
7.5	1800	460	213T	9.1	91.7	91.0	M9911	\$1,515	G4-7U1	Y	200	20.10	PB21A	
7.5	1800	575	213T	7.2	91.7	91.0	M9730	\$1,515	G4-7U1	Y	200	20.10	PB21A	
7.5	1200	230/460	254T	19.6/9.8	91.7	91.0	M9146	\$2,321	G4-7U1	N	315	25.60	PB25A	
7.5	1200	460	254T	9.8	91.7	91.0	M9113	\$2,321	G4-7U1	Y	315	25.60	PB25A	
7.5	1200	575	254T	7.9	91.7	91.0	M9726	\$2,321	G4-7U1	N	315	25.60	PB25A	
7.5	900	230/460	256T	23.2/11.6	89.5	88.5	M9881	\$3,635	G4-7U1	Y	350	25.60	PB25A	
7.5	900	460	256T	11.6	89.5	88.5	M9724	\$3,635	G4-7U1	N	350	25.60	PB25A	
7.5	900	575	256T	9.3	89.5	88.5	M9882	\$3,635	G4-7U1	N	350	25.60	PB25A	
10	3600	230/460	215T	22.4/11.2	91.0	90.2	M9147	\$1,635	G4-7U1	N	220	20.10	PB21A	
10	3600	460	215T	11.2	91.0	90.2	M991	\$1,635	G4-7U1	Y	220	20.10	PB21A	
10	3600	575	215T	9.0	91.0	90.2	M9733	\$1,635	G4-7U1	Y	220	20.10	PB21A	
10	1800	230/460	215T	24.0/12.0	91.7	91.0	M9148	\$1,547	G4-7U1	N	220	20.10	PB21A	
10	1800	460	215T	12.0	91.7	91.0	M9912	\$1,547	G4-7U1	Y	220	20.10	PB21A	
10	1800	575	215T	9.6	91.7	91.0	M9738	\$1,547	G4-7U1	Y	220	20.10	PB21A	
10	1200	230/460	256T	26.0/13.0	91.0	90.2	M9149	\$2,847	G4-7U1	N	350	25.60	PB25A	
10	1200	460	256T	13.0	91.0	90.2	M9114	\$2,847	G4-7U1	Y	350	25.60	PB25A	
10	1200	575	256T	10.5	91.0	90.2	M9737	\$2,847	G4-7U1	N	350	25.60	PB25A	

Notes:
55 TENV Construction