



**Catalog No. SE100J**

**Description: ENCLOSURE OIL/DUST TIGHT 100A (N/KO)**

**UPC No 783164219456**

**Products > Circuit Breakers > Circuit Breaker Enclosures**

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker. Spectra® RMS circuit breakers are suitable for use on AC systems only.

Enclosure notes and/or limitation: Enclosure does not include knockouts (NEMA Type 12).

**ACCESSORIES:**

Neutral Kit (non-GF applications):included

**Descriptors**

Category	Circuit Breaker Enclosures
GO Schedule	B2

**Specifications**

Enclosure Type	NEMA TYPE 12/12K
Mounting	Surface
Frame Type	SE150
Amperage	100 A
UL/CUL Listing	CSA, UL
Material	Steel
Drawings-Outline and Dimensional	139C5653SH2
GSA Compliance	No

**Dimensions**

Height	19.2 in
Depth	4.9 in
Width	9.0 in
Weight	12.4 lb

## Publications

Title	Publication No.	Publication Type
NEMA Type 12 and 12K enclosure, 100 amp max. Product Numbers SE100D, SE100J, TE100D, TE100J, and TB100J. 1 page outline drawing in .pdf format.	139C5653-SH1	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.