



Catalog No. SF250J

Description: ENCLOSURE NEMA 12 NO/KO'S

UPC No 783164219487

Products > Circuit Breakers > Circuit Breaker Enclosures

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker. Spectra® RMS circuit breakers are suitable for use on AC systems only.

Enclosure notes and/or limitation: Enclosure does not include knockouts (NEMA Type 12).

ACCESSORIES:

Neutral Kit (non-GF applications):TNIA225

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B2

Specifications

Enclosure Type	NEMA TYPE 12/12K
Mounting	Surface
Frame Type	SF250
Amperage	250 A
UL/CUL Listing	CSA, UL
Material	Steel
Drawings-Outline and Dimensional	208C2884SH2
GSA Compliance	No

Dimensions

Height	36.2 in
Depth	6.5 in
Width	9.8 in
Weight	26.8 lb

Publications

Title	Publication No.	Publication Type
NEMA Type 12 and 12K enclosure, 250 amp max. Product Number SF250J . 1 page outline drawing in .pdf format.	208C2884-SH2	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.