



Catalog No. TC10324R

Description: 200A 2P DBL THR N3R 120/240V NONFUS

UPC No 783164024838

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Double Throw

- Designed for outdoor rural dwellings and farm buildings to allow connection to a standby generator.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Suitable for use as transfer equipment in standby systems in accordance with Article 702 of the National Electrical Code.
- Non-fusible.
- 60/75°C conductor rating.
- Lockable handle in ON or OFF position.
- Galvanized steel construction.

Descriptors

Category	Double Throw
GO Schedule	SA

Specifications

Voltage	240 AC
Amperage	200 A
Poles	2
Wires	3
Fusing	No Fuse
Enclosure	NEMA 3R (Outdoor)
Options	None
Wire Range (Cu/Al)	6-250
GSA Compliance	Yes

Classifications

CSA Certified	No
UL Listed	Yes

Dimensions

Height	30.2 in
Depth	8.5 in
Width	13.3 in
Weight	38.0 lb

Publications

Title	Publication No.	Publication Type
200A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH131	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.