



Catalog No. TC35325

Description: 400A 3P DBL THR N1 240V NONFUSE

UPC No 783164001723

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Double Throw

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Suitable for use as transfer equipment in standby systems in accordance with Article 702 of the National Electrical Code.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- 60/75 °C conductor rating.
- Full cover interlocks.

Descriptors

Category	Double Throw
GO Schedule	SB

Specifications

Voltage	240 AC
Amperage	400 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 1 (Indoor)
Options	None
Wire Range (Cu/Al)	(2) 1/0-250 (Cu) or 2-600 (Cu)
240 Vac, NEC Std, 3-ph	30.0 hp
GSA Compliance	Yes

Classifications

CSA Certified	No
UL Listed	Yes

Dimensions

Height	34.3 in
Depth	10.3 in
Width	24.5 in
Weight	83.0 lb

Publications

Title	Publication No.	Publication Type
Double-Throw Safety Switch, NEMA 3R 2 pages, 30-400 Ampere Double-Throw Safety Switch	DEH-44154	Installation and Instruction
600A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH122	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.