



## Catalog No. TC35363R

**Description: 100A 3P DBL THR N3R 600V NONFUSE**

**UPC No 783164337396**

**Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Double Throw**

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Suitable for use as transfer equipment in standby systems in accordance with Article 702 of the National Electrical Code.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- 60/75°C conductor rating.
- Full cover interlocks.

### Descriptors

Category	Double Throw
GO Schedule	SB

### Specifications

Voltage	600 AC
Amperage	100 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 3R (Outdoor)
Options	None
Wire Range (Cu/Al)	14-1/0 (Cu)
240 Vac, NEC Std, 3-ph	15.0 hp
480 Vac, NEC Std, 3-ph	15.0 hp
600 Vac, NEC Std, 3-ph	15.0 hp
GSA Compliance	Yes

### Classifications

CSA Certified	No
UL Listed	Yes

### Dimensions

Height	22.9 in
Depth	7.9 in
Width	14.4 in
Weight	39.0 lb

## Publications

Title	Publication No.	Publication Type
<a href="#">Double-Throw Safety Switch, NEMA 1</a> 2 pages, 30-400 Ampere Double-Throw Safety Switch	DEH-44153	Installation and Instruction
<a href="#">200A - Safety Switches</a> 1 page outline drawing in .pdf format.	10103091-SH125	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.