



## Catalog No. TDT3321

Description: 30A 3P DBL THR SS N1 240V FUSIBLE

UPC No 783164069273

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Double Throw

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Suitable for use as transfer equipment in standby systems in accordance with Article 702 of the National Electrical Code.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- 60/75°C conductor rating.
- Full cover interlocks.

### Descriptors

Category	Double Throw
GO Schedule	SB

### Specifications

Voltage	240 AC
Amperage	30 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 1 (Indoor)
Options	None
Wire Range (Cu/Al)	14-8 CU;12-8 AL
240 Vac, Time Delay, 1-ph	3.0 hp
240 Vac, Time Delay, 3-ph	7.5 hp
480 Vac, Time Delay, 1-ph	7.5 hp
480 Vac, Time Delay, 3-ph	15.0 hp
600 Vac, Time Delay, 1-ph	10.0 hp
600 Vac, Time Delay, 3-ph	20.0 hp
250 Vdc	5.0 hp
GSA Compliance	No

### Classifications

CSA Certified	No
UL Listed	Yes

## Dimensions

Height	37.0 in
Depth	9.9 in
Width	12.7 in
Weight	47.0 lb

## Publications

Title	Publication No.	Publication Type
3R, 30A-100A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH137	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.