



Catalog No. TDT3324R

Description: 200A 3P DBL THR SS N3R 240V FUSIBLE

UPC No 783164069396

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Double Throw

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Suitable for use as transfer equipment in standby systems in accordance with Article 702 of the National Electrical Code.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Double Throw
Notes	Not suitable for use as service equipment. Solid neutral not available.
GO Schedule	SB

Specifications

Voltage	240 AC
Amperage	200 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 3R (Outdoor)
Options	None
Wire Range (Cu/Al)	2-250
240 Vac, Time Delay, 1-ph	15.0 hp
240 Vac, Time Delay, 3-ph	60.0 hp
480 Vac, Time Delay, 1-ph	50.0 hp
480 Vac, Time Delay, 3-ph	125.0 hp
600 Vac, Time Delay, 1-ph	50.0 hp
600 Vac, Time Delay, 3-ph	150.0 hp
250 Vdc	40.0 hp
GSA Compliance	No

Classifications

CSA Certified	No
---------------	----

Classifications

UL Listed	No
-----------	----

Dimensions

Height	51.4 in
Depth	11.2 in
Width	11.2 in
Weight	159.0 lb

Publications

Title	Publication No.	Publication Type
3R, 200A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH138	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.