



Catalog No. TDT3324

Description: 200A 3P DBL THR N1 240V FUSIBLE

UPC No 783164069303

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Double Throw

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Suitable for use as transfer equipment in standby systems in accordance with Article 702 of the National Electrical Code.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Double Throw
GO Schedule	SB

Specifications

Voltage	240 AC
Amperage	200 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 1 (Indoor)
Options	None
Wire Range (Cu/Al)	2-250
240 Vac, Time Delay, 1-ph	15.0 hp
240 Vac, Time Delay, 3-ph	60.0 hp
480 Vac, Time Delay, 1-ph	50.0 hp
480 Vac, Time Delay, 3-ph	125.0 hp
600 Vac, Time Delay, 1-ph	50.0 hp
600 Vac, Time Delay, 3-ph	150.0 hp
250 Vdc	40.0 hp
GSA Compliance	No

Classifications

CSA Certified	No
UL Listed	Yes

Dimensions

Height	51.4 in
Depth	11.2 in
Width	20.4 in
Weight	159.0 lb

Publications

Title	Publication No.	Publication Type
3R, 200A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH138	Drawings-Outline and Dimensional
Outline Drawing, 200A Fusible Double Throw Outline Drawing, 200A Fusible Double Throw	10103091SH184	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.