



Catalog No. TDT3361

Description: 30A 3P DBL THR SS N1 600V FUSIBLE

UPC No 783164069440

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Double Throw

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Suitable for use as transfer equipment in standby systems in accordance with Article 702 of the National Electrical Code.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Double Throw
GO Schedule	SB

Specifications

Voltage	600 AC
Amperage	30 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 1 (Indoor)
Options	None
Wire Range (Cu/Al)	14-2
240 Vac, NEC Std, 3-ph	3.0 hp
240 Vac, Time Delay, 3-ph	7.5 hp
480 Vac, NEC Std, 3-ph	5.0 hp
480 Vac, Time Delay, 1-ph	7.5 hp
480 Vac, Time Delay, 3-ph	15.0 hp
600 Vac, NEC Std, 1-ph	3.0 hp
600 Vac, NEC Std, 3-ph	7.5 hp
600 Vac, Time Delay, 1-ph	10.0 hp
600 Vac, Time Delay, 3-ph	20.0 hp
125 Vdc	3.0 hp
250 Vdc	5.0 hp
GSA Compliance	No

Classifications

CSA Certified	No
UL Listed	Yes

Dimensions

Dimensions

Height	37.0 in
Depth	8.3 in
Width	12.0 in
Weight	42.0 lb

Publications

Title	Publication No.	Publication Type
3R, 30A-100A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH137	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.