



Catalog No. TDT3365

Description: 400A 3P DBL THR N1 600V FUSIBLE

UPC No 783164069488

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Double Throw

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Suitable for use as transfer equipment in standby systems in accordance with Article 702 of the National Electrical Code.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Double Throw
GO Schedule	SB

Specifications

Voltage	600 AC
Amperage	400 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 1 (Indoor)
Options	None
Wire Range (Cu/Al)	(2) 1/0-(2) 300 or (1) 1/0-(1) 7506
240 Vac, NEC Std, 3-ph	50.0 hp
240 Vac, Time Delay, 3-ph	125.0 hp
480 Vac, NEC Std, 3-ph	100.0 hp
480 Vac, Time Delay, 3-ph	250.0 hp
600 Vac, NEC Std, 3-ph	125.0 hp
600 Vac, Time Delay, 3-ph	350.0 hp
250 Vdc	50.0 hp
GSA Compliance	No

Classifications

CSA Certified	No
UL Listed	Yes

Dimensions

Height	74.7 in
Depth	8.9 in
Width	25.3 in
Weight	274.0 lb

Publications

Title	Publication No.	Publication Type
600A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH139	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.