



Catalog No. TE100J

Description: ENCLOSURE NEMA 12 100A NO KO

UPC No 783164004885

Products > Circuit Breakers > Circuit Breaker Enclosures

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker.

Frame notes and/or restrictions:3 pole only.

Enclosure notes and/or limitation: Enclosure does not include knockouts (NEMA Type 12).

ACCESSORIES:

Neutral Kit (non-GF applications):included

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B2

Specifications

Enclosure Type	NEMA TYPE 12/12K
Mounting	Surface
Frame Type	E150
Amperage	100 A
UL/CUL Listing	CSA, UL
Material	Steel
Drawings-Outline and Dimensional	139C5653SH2
GSA Compliance	No

Dimensions

Height	19.2 in
Depth	4.9 in
Width	9.0 in
Weight	12.0 lb

Publications

Title	Publication No.	Publication Type
NEMA Type 12 and 12K enclosure, 100 amp max. Product Numbers SE100D, SE100J, TE100D, TE100J, and TB100J. 1 page outline drawing in .pdf format.	139C5653-SH1	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.