



Catalog No. TEB122080

Description: TEB 2 POLE 240V 10K IC 80 AMP

UPC No 783164068702

Products > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

The E150 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 150 Amps and 600 Volts AC. Catalog numbers include the complete breaker or switch. The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs. All TEB, TED, THED breakers suitable for reverse feed. 60/75°C rating through 100 amperes, 75°C rating above 100 amperes.

Descriptors

Category	Thermal Magnetic
GO Schedule	EB

Specifications

Frame Type	E150
Amperage	80 A
Poles	2
Trip Function	LI
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
Submittal Drawing,TEB122080 Breaker,Modular Metering		
Submittal Drawing,TEB122080 Breaker,Modular Metering	DEE-836	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.