



Catalog No. TF225J

Description: ENCLOSURE NEMA 12K 225A SURFACE W/O KO

UPC No 783164007367

Products > Circuit Breakers > Circuit Breaker Enclosures

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker.

Enclosure notes and/or limitation: Enclosure does not include knockouts (NEMA Type 12).

ACCESSORIES:

Neutral Kit (non-GF applications):TNIA225

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B2

Specifications

Enclosure Type	NEMA TYPE 12/12K
Mounting	Surface
Frame Type	F225
Amperage	225 A
UL/CUL Listing	CSA, UL
Material	Steel
Drawings-Outline and Dimensional	139C5682SH2
GSA Compliance	No

Dimensions

Height	31.7 in
Depth	6.4 in
Width	9.5 in
Weight	23.2 lb

Publications

Title	Publication No.	Publication Type
NEMA Type 12 and 12K enclosure, 225 amp max. Product Numbers TF225D and TF225J. 1 page outline drawing in .pdf format.	139C5682-SH2	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.