



Catalog No. TFN60RGFR

Description: GE 60A GD ACD NF 15A GFI 10HP STEEL N3R

UPC No 783164343113

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Puller Type AC Disconnect

60 Amp Non-Fusible General Duty Steel Disconnect with GFCI outlet

Descriptors

Category	Puller Type AC Disconnect
GO Schedule	RX

Specifications

Voltage	240 Vac
Amperage	60 A
Fusing	No Fuse
Enclosure	NEMA Type 3R
Wire Range (Cu/Al)	14-3 Cu/Al
GSA Compliance	No

Classifications

UL Listed	CULUS Listed
-----------	--------------

Dimensions

Height	7.1 in
Depth	5.2 in
Width	5.5 in

Publications

Title	Publication No.	Publication Type
GE 60A GD AC DISCONNECT OUTLINE DRAWING	TFN60RGFR	Drawings-Outline and Dimensional
GE 60A GD AC DISCONNECT PULLER-TYPE 240V NON-FUSIBLE 10HP 15A GFI RECEPT STEEL N3R ENCL OUTLINE DRAWING		

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.