



Catalog No. TH3361JW

Description: 30A 3P HD N5/12 600V FUSIBLE WIN

UPC No 783164065060

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	30 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 5, 12 Drip/Dust-tight
Options	Viewing Window
Wire Range (Cu/Al)	12-2
240 Vac, Time Delay, 3-ph	7.5 hp
480 Vac, NEC Std, 1-ph	3.0 hp
480 Vac, NEC Std, 3-ph	5.0 hp
480 Vac, Time Delay, 1-ph	7.5 hp
480 Vac, Time Delay, 3-ph	15.0 hp
600 Vac, NEC Std, 1-ph	3.0 hp
600 Vac, NEC Std, 3-ph	7.5 hp
600 Vac, Time Delay, 1-ph	10.0 hp
600 Vac, Time Delay, 3-ph	20.0 hp
250 Vdc	5.0 hp
GSA Compliance	Yes

Classifications

CSA Certified	No
UL Listed	Yes

Dimensions

Height	13.3 in
--------	---------

Dimensions

Depth	5.4 in
Width	9.4 in
Weight	16.0 lb

Publications

Title	Publication No.	Publication Type
60A (incl. -R suffix) - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH110	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.