



Catalog No. TH3361SSW

Description: 30A 3P HD N4X SS316 600V FUSIBLE WIN

UPC No 783164065022

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	30 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 4/4X Water/Dust-tight
Options	Viewing Window
Wire Range (Cu/Al)	14-6
240 Vac, Time Delay, 3-ph	7.5 hp
480 Vac, NEC Std, 1-ph	3.0 hp
480 Vac, NEC Std, 3-ph	5.0 hp
480 Vac, Time Delay, 1-ph	7.5 hp
480 Vac, Time Delay, 3-ph	15.0 hp
600 Vac, NEC Std, 1-ph	3.0 hp
600 Vac, NEC Std, 3-ph	7.5 hp
600 Vac, Time Delay, 1-ph	10.0 hp
600 Vac, Time Delay, 3-ph	20.0 hp
125 Vdc	2.0 hp
250 Vdc	5.0 hp
GSA Compliance	Yes

Classifications

CSA Certified	Yes
UL Listed	Yes

Dimensions

Height	13.3 in
Depth	4.9 in
Width	9.4 in
Weight	18.0 lb

Publications

Title	Publication No.	Publication Type
60A (incl. 316 Stainless) - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH109	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.