



Catalog No. TH3364JR

Description: 200A 3P HD N3R/5/12 600V FUSIBLE

UPC No 783164064056

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	200 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 3R,5,12 Outdr/Drp/Dst
Options	None
Wire Range (Cu/Al)	2-250
480 Vac, NEC Std, 1-ph	25.0 hp
480 Vac, NEC Std, 3-ph	50.0 hp
480 Vac, Time Delay, 1-ph	50.0 hp
480 Vac, Time Delay, 3-ph	125.0 hp
600 Vac, NEC Std, 1-ph	30.0 hp
600 Vac, NEC Std, 3-ph	60.0 hp
600 Vac, Time Delay, 1-ph	50.0 hp
600 Vac, Time Delay, 3-ph	150.0 hp
250 Vdc	40.0 hp
GSA Compliance	Yes

Classifications

CSA Certified	Yes
UL Listed	Yes

Dimensions

Height	35.1 in
--------	---------

Dimensions

Depth	5.0 in
Width	14.5 in
Weight	49.0 lb

Publications

Title	Publication No.	Publication Type
200A (incl. -R suffix) - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH120	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.