



Catalog No. TH4364C

Description: 200A 3P HD N1 600V FUSIBLE CSA

UPC No 783164422450

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Suitable for use as service equipment when installed in accordance with the Canadian Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	200 A
Poles	3
Wires	4
Fusing	Fusible
Enclosure	NEMA 1 (Indoor)
Options	CSA SE Rated
Wire Range (Cu/Al)	2-250
480 Vac, NEC Std, 1-ph	25
480 Vac, NEC Std, 3-ph	50
480 Vac, Time Delay, 1-ph	50
480 Vac, Time Delay, 3-ph	125
600 Vac, NEC Std, 1-ph	30
600 Vac, NEC Std, 3-ph	60
600 Vac, Time Delay, 1-ph	50
600 Vac, Time Delay, 3-ph	150
250 Vdc	40
GSA Compliance	No

Classifications

CSA Certified	Yes
UL Listed	No

Dimensions

Height	31.5
Depth	5.1
Width	13.3

Dimensions

Weight

32

Publications

Title	Publication No.	Publication Type
200A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH105	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.